

**Part Number :** [732510191](#)

**Product Description :** SMA Plug, Right-Angle, Crimp, RG-141, RG-303 and RG-58 Cable, Crimp, Body Passivated Stainless Steel, 50 Ohms

**Series Number :** 73251

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents and Resources

### Drawings

[732510191\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per per ED/01/2017 (12 January 2017)  |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

|              |   |
|--------------|---|
| Status       | Active  |
| Category     | RF / Coaxial Connectors   |
| Series       | 73251   |
| Description  | SMA Plug, Right-Angle, Crimp, RG-141, RG-303 and RG-58 Cable, Crimp, Body Passivated Stainless Steel, 50 Ohms |
| Application  | RF  |
| Product Name | SMA   |
| Style        | Cable   |
| Type         | Subminiature  |
| UPC          | 800756015231  |

### Electrical

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 18 GHz                      |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 500 Vrms@Sea Level |

### Physical

|                       |             |
|-----------------------|-------------|
| Cable Attachment      | Crimp       |
| Gender                | Plug        |
| Keying to Mating Part | N/A         |
| Net Weight            | 5.361/g     |
| Orientation           | Right Angle |
| Packaging Type        | Bag         |

|                    |                                |
|--------------------|--------------------------------|
| Panel Mount        | No                             |
| Panel Mount Method | N/A                            |
| PCB Mounting       | N/A                            |
| Reverse Polar      | No                             |
| Wire/Cable Type    | RG-58, RG-141, RG-303, LMR-195 |

---

This document was generated on Jan 04, 2026