
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC	DIST
DY	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NPR PER ECR-10-016899	13AUG2010	SYJ	LSF



RECOMMENDED P.C.BOARD LAYOUT



SECT."A"-"A"
(SCALE 10-1)

NOTES:

1. MATERIAL:
   HOUSING: L.C.P. (HIGH TEMP. THERMOPLASTIC) UL 94V-0,NATURAL.
   CONTACT: COPPER ALLOY.
2. FINISHI:
   CONTACT AREA: 0.00038 MIN GOLD ON 0.0013 MIN ALL OVER NICKEL.
   SOLDERING AREA:0.002 MIN MATTE-TIN.
3. POSITION SERIES: SEE TABLE.
4. CONN STACK HEIGHT COMBINE OF PLUG "Y"H VS REC "X"H.
   STACK HEIGHT = Y + X - 5

P/N SEE SHEET 2 OF 2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.30
2 PLC	±0.25
3 PLC	±0.20
4 PLC	±-
ANGLES	±3°

MATERIAL -

FINISH -

DWN YJ SEE	18MAY2010
CHK SF LEONG	
APVD SF LEONG	
PRODUCT SPEC 108-5390	
APPLICATION SPEC 114-5254	
WEIGHT -	

Tyco Electronics
Tyco Electronics Singapore

NAME
REC ASSY
FOR FH 0.8BTB CONNECTOR 5.6H
0.5 BOSS LENGTH (0.38um GOLD)

SIZE	CAGE CODE	DRAWING NO
A3	00779	C-1735881

CUSTOMER DRAWING

SCALE	SHEET	REV
4:1	1 OF 2	A


Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST
DY	-


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





DETAIL B



DETAIL A
(SCALE 4-1)

NOT AVAILABLE	650	16	88	84.4	42.2	60.2	61.8	55.2	140	1735881-6
AVAILABLE	650	16	72	68.4	34.2	52.2	53.8	47.2	120	1735881-5
NOT AVAILABLE	650	16	72	68.4	34.2	44.2	45.8	39.2	100	1735881-4
	900	12	56	52.4	26.2	36.2	37.8	31.2	80	1735881-3
	900	12	44	40.4	20.2	28.2	29.8	23.2	60	1735881-2
	900	12	32	28.4	14.2	20.2	21.8	15.2	40	1735881-1
REMARKS	QTY	AE	AC	AB	AA	C	B	A	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.30
2 PLC	±0.25
3 PLC	±0.20
4 PLC	±-
ANGLES	±3°

MATERIAL -

FINISH -

DWN YJ SEE 18MAY2010
CHK SF LEONG
APVD SF LEONG
PRODUCT SPEC 108-5390
APPLICATION SPEC 114-5254
WEIGHT -

Tyco Electronics
Tyco Electronics Singapore

NAME
REC ASSY
FOR FH 0.8BTB CONNECTOR 5.6H
0.5 BOSS LENGTH (0.38um GOLD)

SIZE	CAGE CODE	DRAWING NO
A3	00779	C-1735881

CUSTOMER DRAWING

SCALE 4:1 SHEET 2 OF 2 REV A

Downloaded from Arrow.com.