Part Number : 2008900102
Product Description : 2.00mm Pitch EdgeLock Wire-to-Board Edge Card Connector, 1.60mm PCB Thickness, Nylon, Low-Halogen, UL94-V0, 2 Circuits, Natural
Series Number : 200890
Status : Active
Product Category : Card Edge Connectors



Documents and Resources

Drawings

2008900102_sd.pdf

2008900001PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2008900001PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Card Edge Connectors
Series	200890
Description	2.00mm Pitch EdgeLock Wire-to-Board Edge Card Connector, 1.60mm PCB Thickness, Nylon, Low-Halogen, UL94-V0, 2 Circuits, Natural
Component Type	Edgecard to Wire
Product Name	EdgeLock
UPC	191128189255

Agency

UL	E29179

Electrical

Current - Maximum per Contact	3.0A
Data Rate	Unrated
High Power Bay (30.0A or more)	No
Voltage - Maximum	125V

Physical

Downloaded from Arrow.com.

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Durability (mating cycles max)	30
Edge Card Thickness	N/A
Entry Angle	90° Angle (Side Entry)
Flammability	94V-0
Keying to Mating Part	No
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	1.400/g
Orientation	Right Angle
Packaging Type	Bag
Panel Mount	No
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm
(p)ower-(s)ignal Configuration	2s - 0p
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Straddle Mount-Edge Card

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Edge Card PCB

Use with Part(s)

Description	Part Number
2.00mm Pitch EdgeLock Crimp Terminal, Phosphor Bronze, Tin (Sn) Plating,Reel	2004490001

Downloaded from Arrow.com.