Part Number : 638235100
Product Description : PremiumGrade Hand Crimp Tool for Micro-Latch, DuraClik, and Servo Motor Encoder Female Terminals, 26-22 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATS-638235100-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for Micro-Latch, DuraClik, and Servo Motor Encoder Female Terminals, 26-22 AWG
Comments	See Tooling Specification (PDF) Above; Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	884982203143

Downloaded from Arrow.com.

Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	317.100/g

Applicable Parts

Description	Part Number
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 26-22 AWG, Reel	503728000
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 26-22 AWG, Bag	503728100
2.00mm Pitch DuraClik Crimp Terminal, Female, 26-22 AWG, Gold (Au) Plating, Reel	561618081
2.00mm Pitch DuraClik Crimp Terminal, Female, 26-22 AWG, Gold (Au) Plating, Bag	561618181
DuraClik Crimp Terminal, Female, 26-22 AWG, Tin (Sn) Plating, Reel	5600850101

Downloaded from Arrow.com.

This document was generated on Sep 10, 2026

Downloaded from Arrow.com.