



1		2		3		4		5		6		7		8	
A	36	09457151578		RJ45 Ethernet stranded cable, AWG 26/7, 4x2x0.5/1.0, Cat. 6A, PUR, yellow		Ø6.7		100							
	35	09457151577						40							
	34	09457151576						30							
	33	09457151575						25							
	32	09457151574						20							
	31	09457151573						15							
	30	09457151572						10							
	29	09457151571						9							
	28	09457151570						8							
	27	09457151569						7							
	26	09457151568						6							
	25	09457151567						5							
	24	09457151566						4							
	23	09457151565						3							
	22	09457151564						2							
	21	09457151563						1.5							
	20	09457151562						1							
	19	09457151561						0.5							
D	18	09457151553		RJ45 Ethernet stranded cable, AWG 26/7, 4x2x0.5/1.0, Cat. 6A, PVC, yellow		Ø6.6		20							
	17	09457151552						15							
	16	09457151551						10							
	15	09457151532						30							
	14	09457151531						9							
	13	09457151530						8							
	12	09457151529						7							
	11	09457151528						6							
	10	09457151527						5							
	9	09457151535						4.4							
	8	09457151526						4							
	7	09457151534						3.4							
	6	09457151525						3							
	5	09457151533						2.2							
	4	09457151524						2							
	3	09457151523						1.5							
	2	09457151522						1							
	1	09457151521						0.5							
F	Cont. no.	Part no.		Type of cable		Dim. d [mm]		Dim. a[m]							

50	09457151594		RJ45 Ethernet stranded cable, 4x2xAWG 26/7, PVC, outdoor, Cat. 6A, black		Ø6.6		20			
49	09457151593						15			
48	09457151592						10			
47	09457151591						9			
46	09457151590						8			
45	09457151589						7			
44	09457151588						6			
43	09457151587						5			
42	09457151586						4			
41	09457151585						3			
40	09457151584						2			
39	09457151583						1.5			
38	09457151582						1			
37	09457151581						0.5			
Cont. no.	Part no.		Type of cable		Dim. d [mm]		Dim. a[m]			

		All rights reserved		Created by STOCHECIC		Inspected by COSTEA		Standardisation MUNTEANV		Date 2018-04-19		State Final Release			
HARTING Customised Solutions		Department HCS - RO		Title Han 3A RJ45 Cable Assembly								Doc-Key / ECM-Nr. 100155415/UGD/012/H 500000133904			
D-32339 Espelkamp				Type TB		Number 094571515XX						Rev. H		Page 2/2	