

HC-STA-B16-HHFS-1STP21-EL-AL - Housing



1412683

<https://www.phoenixcontact.com/us/products/1412683>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B16, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x Pg21, height: 76 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1412683
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 620 (C-2-2019)
GTIN	4055626059778
Weight per piece (including packing)	223 g
Weight per piece (excluding packing)	233 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B16-HHFS-1STP21-EL-AL - Housing



1412683

<https://www.phoenixcontact.com/us/products/1412683>

Technical data


Notes

General	For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K
General	also available as a powder-coated or color version: 1373008 HC-STA-B16-HHFS-1STP21-EL/...

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B16
No. of cable outlets	1
Type of the screw connection	1x Pg21
Type	Tall design
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	44 mm
Height	76 mm
Length	93.5 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data	
Type of the screw connection	1x Pg21
Locking type	Pin

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)

HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B16-HHFS-1STP21-EL-AL - Housing


1412683

<https://www.phoenixcontact.com/us/products/1412683>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B16-HHFS-1STP21-EL-AL - Housing



1412683

<https://www.phoenixcontact.com/us/products/1412683>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412683>



DNV
Approval ID: TAE000037S



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026



EAC
Approval ID: RU C-DE.AI30.B.01102



EAC
Approval ID: RU C-DE.BL08.B.00511

cULus Recognized

HC-STA-B16-HHFS-1STP21-EL-AL - Housing



1412683

<https://www.phoenixcontact.com/us/products/1412683>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



Accessories

G-INS-PG21-M68N-NNES-S - Cable gland

1411175

<https://www.phoenixcontact.com/us/products/1411175>



Cable gland, material for screw connection: Brass, nickel-plated, application: Standard, external cable diameter 13 mm ... 18 mm, shielding: no, connecting thread: Pg21, color: silver, with O-ring

G-INSEC-PG21-M68N-NNES-S - Cable gland

1411200

<https://www.phoenixcontact.com/us/products/1411200>



Cable gland, material for screw connection: Brass, nickel-plated, application: EMC, external cable diameter 13 mm ... 18 mm, shielding: yes, connecting thread: Pg21, color: silver, with O-ring

HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



US-EMLP (20X9) CUS - Plastic label

0830085

<https://www.phoenixcontact.com/us/products/0830085>

Plastic label, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, lettering field size: 20 x 9 mm, Number of individual labels: 75



HC-B16-HCWS-PLR-BK - Protective cover

1346541

<https://www.phoenixcontact.com/us/products/1346541>

Protective cover B16, with single locking latch, protective cover material: PC, height: 26.3 mm, seal: yes



HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



US-EMLP-HA (20X9) - Plastic label

0830989

<https://www.phoenixcontact.com/us/products/0830989>



Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 20 x 9 mm, Number of individual labels: 70

WP-G HF IP66 PG21 BK - Screw connection

3240892

<https://www.phoenixcontact.com/us/products/3240892>



Cable gland, Pg thread, IP66 protection, straight

HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



WP-G HF IP69K PG21 BK - Screw connection

3240878

<https://www.phoenixcontact.com/us/products/3240878>

Cable gland, Pg thread, IP68/69k protection, straight



WP-GA HF IP66 PG21 BK - Screw connection

3240920

<https://www.phoenixcontact.com/us/products/3240920>

Cable gland, Pg thread, IP66 protection, angled



HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



WP-GR HF IP66 PG21 BK - Screw connection

3240948

<https://www.phoenixcontact.com/us/products/3240948>



Cable gland, Pg thread, IP66 protection, with strain relief

WP-GR HF IP69K PG21 BK - Screw connection

3240934

<https://www.phoenixcontact.com/us/products/3240934>



Cable gland, Pg thread, IP68/69k protection, with strain relief

HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



WP-G PP HF PG21 - Screw connection

3240992

<https://www.phoenixcontact.com/us/products/3240992>

Cable gland made from PP with Pg thread, IP65 protection



WP-GT PP HF PG21 - Screw connection

3241006

<https://www.phoenixcontact.com/us/products/3241006>

Cable gland made from PP with Pg thread, rotatable, IP54 protection



HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



WP-G BRASS IP40 PG21 - Screw connection

3241041

<https://www.phoenixcontact.com/us/products/3241041>

Cable gland made from brass with Pg thread, IP40 protection



WP-GT BRASS PG21 - Screw connection

3241027

<https://www.phoenixcontact.com/us/products/3241027>

Cable gland made from brass with Pg thread, rotatable, IP40 protection



HC-STA-B16-HHFS-1STP21-EL-AL - Housing

1412683

<https://www.phoenixcontact.com/us/products/1412683>



WP-G BRASS IP65 PG21 - Screw connection

3241055

<https://www.phoenixcontact.com/us/products/3241055>

Cable gland made from brass with Pg thread, IP65 protection



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com