


[Printer Labels](#) / [Bradyprinter PR Plus Printer Labels](#) /

3" Core Series UltraTemp Gloss Polyimide Labels

3" Core Series UltraTemp Gloss Polyimide Labels



Product Highlights:

Label/Tape Size:

0.25 in H x 0.25 in W

Material:

Polyimide

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series
Label Printer, BradyPrinter i5100,
BradyPrinter i7100, BRADYPRINTER PR
Plus Series Label Printer, THT 3" Core
Printer

Material Number:

B-727

Color:

White

Quantity per Roll:

20000

Part Number:

THT-70-727-20

ADD TO CART

1



Add To Favorites

Need a different size? Customize it!

PEOPLE ALSO VIEWED

OVERVIEW

High Temperature Polyimide (B-727) withstands wave solder environments and multiple harsh washes for printed circuit board and electronic component preprocess labeling.

- ultra-durable adhesive is designed for use with extreme wash protocol and cleaning chemicals, and is ideal for use in auto apply equipment
- Glossy white polyimide material is thermal transfer printable

- RoHS compliant to 2011/65/EU; UL Approved; Meets requirements of MIL-STD-202C, Method 215K
- Service temperature of -94 to 212° F (-70 to 100° C)

SPECIFICATIONS

Material Number	B-727
Catalog Page #	177
Dimensions	0.25 in H x 0.25 in W
UOM	Roll of 20000 Labels
Finish	Gloss
Label/Tape Size	0.25 in H x 0.25 in W
Maximum Service Temperature °F	572 °F
Meta Description	Brady THT-70-727-20 is a High-Temperature Industrial Polyimide Barcode Label that is 0.250" X 0.250" (6.350 mm X 6.350 mm). Shop online!
Meta Title	BRADY THT-70-727-20 INDUSTRIAL BARCODE LABEL
Minimum Service Temperature °F	-94 °F
Printable Area Dimensions	0.25 in H x 0.25 in W
Printable Area Height	0.25 in
Printable Area Width	0.25 in
Product Number	132492
UPC	754473847449
Quantity per Roll	20000
Quantity per Row	7
Secondary Label Included	Secondary Label is Not Included
Thickness	0.0044 in
Trade Name	UltraTemp®
Unit Price	/Label
Adhesive Type	Acrylic
Applications	Circuit Board ID - After Process, Circuit Board ID - Surface Mount, Circuit Board ID - Through Hole Bottom, Circuit Board ID - Through Hole Top, Component & Equipment ID
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer
Label/Media Format	Roll

Label Properties	Heat Resistant Labels, Permanent Adhesive Labels
Material	Polyimide
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant
Shape	Square
Suggested Ribbon Series	R6000

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate

[About](#)

[Careers](#)

[Investors](#)

[Privacy](#)

[Policy](#)

[Terms and](#)

[Conditions](#)

[Terms of](#)

[Use](#)

[ISO](#)

[Certificates](#)

Other BradyContact

[Sites](#)

[Distributor](#)

[Portal](#)

[International](#)

[Sites](#)

[Safety](#)

[Services &](#)

[Software](#)

[Smart ID](#)

[Brand](#)

[Protection](#)

[Solutions](#)

[6555 W.](#)

[Good Hope](#)

[Rd.](#)

[Milwaukee,](#)

[WI 53223](#)

[Phone: 888-](#)

[250-3082](#)

[Hours: 7am-](#)

[6pm CT](#)

[Monday -](#)

[Thursday;](#)

[Friday 7am-](#)

[5pm CT](#)

Brady (NYSE:BRC) is a

manufacturer of complete

solutions that identify and

protect people, products and

places. Brady's products help

customers increase safety,

security, productivity and

performance and include high-

performance labels, signs, safety

devices, printing systems and

software.



2018 © Brady Worldwide, Inc.