Part Number : 431784002
Product Description : Sabre Crimp Terminal, Male, 20-18 AWG, 2.50-2.85mm max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact
Series Number : 43178
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

431784002_sd.pdf

431780000-PK-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-44441-9999-001.pdf

444410000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	43178
Description	Sabre Crimp Terminal, Male, 20-18 AWG, 2.50-2.85mm max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact
Application	Wire-to-Wire
Product Name	Sabre
UPC	884982063945

Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.550/g
Packaging Type	Reel
Plating min - Mating	0.508µm

Downloaded from Arrow.com.

Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.50-2.85mm
Wire Size (AWG)	18, 20
Wire Size mm^2	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sabre Female Crimp Terminals	43375

Use with Part(s)

Description	Part Number
Sabre Plug Crimp Housings	43680

Application Tooling

Global

Description	Part Number
Manual Activation and Deactivation Tool	638130600
Manual Extraction Tool	638130800
Hand Crimp Tool for Crimp Terminals	638233300
FineAdjust Applicator for Male Flat Blade Crimp Terminals	639013300
T2 Terminator	639113300

Downloaded from Arrow.com.