

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0340833003

Status:

Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Cable Seal Female Terminal, Tin Plating, 22 AWG, Left Reel Payoff

Documents:

- Drawing (PDF)

Product Specification PS-34083-002-001 (PDF)

Application Specification AS-34083-002-001 (PDF)

Packaging Specification 313025040-000 (PDF)
- Test Summary TS-34083-002-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Crimp Quality Equipment

Overview

Product Name

UPC

Crimp Terminals

34083

Power, Wire-to-Board, Wire-to-Wire

Left Reel Payoff, Cable Seal

Yes

MX150 Sealed and Unsealed Connector System

MX150

822350084550

Physical

Gender

Grip Code

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

22

High Performance Alloy (HPA)

Tin

Tin

0.387/g

Reel

0.508µm

0.508µm

Crimp or Compression

1.70mm max.

22

0.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

Contact Molex

14V DC

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

Test Summary

AS-34083-002-001

313025040-000

PS-34083-002-001

SD-34083-002-001

TS-34083-002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

34083 Series

Use With

MX150 Cable Sealed Female Connector
34062 , 34250

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Toolkit for MX150 Connectors

FA2 Mechanical Feed Applicator for MX150 22 Grip Wire Seal Receptacle Terminal, 0.35mm²

FA2 Pneumatic Feed Crimp Applicator for MX150 Female

2002220700

638083000

638083010

Wire Seal Terminals,
0.35mm² Wire
FA2 Mechanical 638088000
Feed Applicator
for MX150 22 Grip
Receptacle Wire
Seal Terminals, 22
AWG and 0.50mm²
Wires
FA2 Pneumatic Feed 638088010
Crimp Applicator
for MX150 22 Grip
Receptacle Wire
Seal Terminals, 22
AWG and 0.50mm²
Wires
Extraction Tool for 638131500
MX150L, MX150, PT
Bulb Socket, iGrid,
SPOX, and Wire-to-
Motor Terminals
Hand Crimp Tool for 638199300
Cable Seal Crimp
Terminals

This document was generated on 03/02/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION