

+ SHIPS FREE
 UPS FLAT RATE
MILITARY DISCOUNT
IBEW-NECA DISCOUNT

[Account](#) | [Wishlist](#) | [Quick Order](#) | [Log In](#)
 100% Lifetime Guarantee

[Best Sellers](#) [On Sale](#)
[Home](#) → [Tool Types](#) → [Screwdrivers](#) → [Slotted SoftFinish® Screwdrivers](#)

Slotted SoftFinish® Screwdrivers



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.
[Be the first to review this product](#)

 Filter:

SKU	Product	Slotted Tip Thickness MM	Profile Tip Features	Blade Length Inch	OAL MM	Price	Qty
30202	SoftFinish® Slotted Driver 2.0 x 65mm	0.4	Cabinet Tip	2.6	169		<input type="button" value="0"/> 
30203	SoftFinish® Slotted Driver 2.5 x 75mm	0.4	Cabinet Tip	3	179		<input type="button" value="0"/> 
30204	SoftFinish® Slotted Driver 3.0 x 80mm	0.5	Cabinet Tip	3.1	184		<input type="button" value="0"/> 
30205	SoftFinish® Slotted Driver 3.0 x 100mm	0.5	Cabinet Tip	3.9	204		<input type="button" value="0"/> 
30206	SoftFinish® Slotted Driver 3.0 x 150mm	0.5	Cabinet Tip	5.9	254		<input type="button" value="0"/> 
30208	SoftFinish® Slotted Driver 3.0 x 200mm	0.5	Cabinet Tip	8	304		<input type="button" value="0"/> 
30210	SoftFinish® Slotted Driver 3.5 x 100mm	0.6	Cabinet Tip	3.9	204		<input type="button" value="0"/> 
30211	SoftFinish® Slotted Driver 4.5 x 125mm	0.8	Cabinet Tip	5	236		<input type="button" value="0"/> 

SKU	Product	Slotted Tip Thickness MM	Profile Tip Features	Blade Length Inch	OAL MM	Price	Qty
30212	SoftFinish® Slotted Driver 3.5 x 200mm	0.6	Cabinet Tip	8	304		0 
30215	SoftFinish® Slotted Driver 4.0 x 100mm	0.8	Cabinet Tip	3.9	211		0 
30216	SoftFinish® Slotted Driver 4.0 x 200mm	0.8	Cabinet Tip	8	311		0 
30217	SoftFinish® Slotted Driver 4.0 x 150mm	0.8	Cabinet Tip	5.9	261		0 
30218	SoftFinish® Slotted Driver 4.5 x 80mm	0.8	Cabinet Tip	3.1	191		0 
30219	SoftFinish® Slotted Driver 4.5 x 150mm	0.8	Cabinet Tip	5.9	261		0 
30220	SoftFinish® Slotted Driver 5.5 x 125mm	1	Cabinet Tip	5	236		0 
30221	SoftFinish® Slotted Driver 5.5 x 200mm	1	Cabinet Tip	8	311		0 
30238	SoftFinish® Slotted Driver 5.5 x 300mm	1	Cabinet Tip	11.8	411		0 
30222	SoftFinish® Slotted Driver 6.0 x 100mm	1.2		3.9	218		0 
30223	SoftFinish® Slotted Driver 6.5 x 100mm	1		3.9	218		0 
30225	SoftFinish® Slotted Driver 6.5 x 150mm	1.2		5.9	268		0 
30226	SoftFinish® Slotted Driver 6.5 x 200mm	1.2		8	318		0 
30227	SoftFinish® Slotted Driver 8.0 x 150mm	1.2		5.9	274		0 
30230	SoftFinish® Slotted Driver 8.0 x 175mm	1.2		7	299		0 
30232	SoftFinish® Slotted Driver 8.0 x 300mm	1.2		11.8	424		0 
30235	SoftFinish® Slotted Driver 10.0 x 200mm	1.6		8	324		0 
30236	SoftFinish® Slotted Driver 12.0 x 250mm	2		9.8	374		0 

[Add to Cart](#)



We accept



Details

Wiha SoftFinish Handle

- › Dual material molded improves comfort and performance.
- › Through ergonomic design the handle allows 40% more torque and less hand fatigue than conventional handles.
- › Handle with roll-off protection feature.

Wiha Screwdriver Tips

- › Wiha tips are precision machined to exact tolerances for a perfect fit every time.
- › Wiha utilizes an exclusive chrome-vanadium-molybdenum tool steel.
- › Through hardened to 60 on the Rockwell C scale.

Wiha Hard Chromtop Plating

- › Provides additional unmatched durability for tips and blade integrity.

Additional Info

Head Type	⊖ ⊖ slotted
Country of Manufacture	Germany
Handle Grip Types	SoftFinish - cushioned
Steel HRC	60

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



SoftFinish® Slotted/Phillips/Square
Screwdriver 10 Piece Set

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels assure products consistent

with our reputation for outstanding performance in demanding service, repair and production applications.

Discounts and promotions

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH Schonach Germany](#)

Monday - Friday Office Hours 7am - 5pm CST USA

1348 Dundas Cir,

Monticello, MN 55362

Customer Service Email: cservice@wihatools.com

Tel: [763-295-6591](tel:763-295-6591)

Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

Over 5000 Professional Quality Wiha Tools In Stock



Newsletter

[Subscribe](#)