

08095500 & ... BATTERY DISCONNECT SWITCHES

Accessories for electrical battery disconnect switches



08095500



00225800



00603800



00902900



00226200



00226600



00227400



00900400



00900500



00900600



00900700



00900900



00901600



00901900



00903100

Ordering Information

PART NUMBER	PACKAGING CONTENT	DESCRIPTION	MATERIAL	BATTERY SWITCHES APPLICATION
08095500	2 pcs.	Rubber protection cap	Grommet	M10-M12 contact
00225800	2 pcs.	Stiff protection sheath for NW17 corrugated pipe	Plastic	08094461-08094562-08094563
00603800	10 pcs.	Rubber protection cap	Grommet	08094461-08094562-08094563
00901900	1 pcs.	Changeover Button	Plastic	08075100-08075162
00902900	1 pcs.	Protection cover	Plastic	08094561-08094860-08094960
00226200	2 pcs.	Stiff protection sheath for NW22 corrugated pipe	Plastic	08097362-08097461-08097462
00226600	2 pcs.	Stiff protection sheath closed	Plastic	08091761
00227400	1 pcs.	8-pole plug (8x1,6 mm)	Plastic	08097860-08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096590
00900400	1 pcs.	Black button for activation	Metal	08070000-08070100-08070060-08070160-08094270-08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096590-08096561-08096562-08096563
00900500	1 pcs.	Protection cover for emergency switch on-cab with screws	Plastic	Electrical battery switches
00900600	1 pcs.	Metallic bracket	Metal	08098100
00900700	1 pcs.	Metallic bracket	Metal	08098100
00900900	1 pcs.	Emergency switch-on red button	Metal	Electrical battery switches
00901600	1 pcs.	Double pole changeover button	Metal	Magnetic battery switches retention
00902800	1 pcs.	Protection cover	Plastic	08098160-08097368-08097468
00903100	1 pcs.	Electrical wiring with 7 pole	-	08097362-08097461-08097462-08097363-08097463-08097367-08097467-08097469

08095500 & ... BATTERY DISCONNECT SWITCHES

Accessories for electrical battery disconnect switches



Ordering Information

PART NUMBER	PACKAGING CONTENT	DESCRIPTION	MATERIAL	BATTERY SWITCHES APPLICATION
08095400	1 pcs.	Electrical wiring with 8 pole	-	08097860-08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096591-08096562-08096590
00226800	1 pcs.	4-pole plug according DIN 72585	Plastic	08097161-08097262-08091761-08097460-08097464-08097364
00227300	1 pcs.	7-pole plug	Plastic	0809736-08097367-08097463-08097467-08097469
00227700	1 pcs.	4-pole male connector	Plastic	08070000-08070100-08070060-08070160
00227100	1 pcs.	Stiff protection sheath	Plastic	08096561
00227900	1 pcs.	8-pole plug (7x1,6 mm +1x3,5 mm)	Plastic	08096563
00900800	1 pcs.	Green control light (LED)	-	08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096591-08096562-08096590
00901000	1 pcs.	Green button for battery switch activation	Metal	ADR version
08096300	1 pcs.	P.V.M. 4 module	-	ADR version
07590700	1 pcs.	Earth contact strip length 880 mm section mm² 20	Copper moulded	ADR version
00226700	2 pcs.	Stiff protection sheath	Plastic	08097469
00901400	1 pcs.	Metallic bracket	Metal	08097364-08097464
00901500	1 pcs.	Change over contact (ON)-OFF-(ON)	Plastic	08097367-08097463-08097467-08097469-08097363
00121400	1 pcs.	1A fuse holder for ADR application	Plastic	ADR version
00712500	1 pcs.	4 pole plug female wiring	-	08075161-08075163 (WatchDog)
00712600	1 pcs.	7 pole plug female wiring	-	08075161-08075163 (WatchDog)