


1326122-1 Product Details

 Share  Print  Email



 Active

 View 3D PDF

0.64 mm Connector Systems

52WAY LAC "SINGLE GEAR" SHIELD

1326122-1 

TE Internal Number: 1326122-1

Product Highlights [View All](#)

- Product Series = AMP 0.64 mm
- Wire-to-Wire
- Applies To Wire/Cable
- Backshell/Cable Clamp
- For Use With Receptacle: 1326042

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through
Distributor

Feedback

DocumentsFeaturesCompliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Series	AMP 0.64 mm
Product Type	Backshell/Cable Clamp
Sealed	No

Mechanical Attachment

Panel Mount Retention	Without
Mating Retention Type	Latch(ing)

Electrical Characteristics

Operating Voltage Reference	DC
-----------------------------	----

Body Features

Cable Exit Angle	70°
Assembly Integration Feature	With
Assembly Integration Type	Lever
Mating Retention	With
Shield Color	Black

Contact Features

Multiple Contact Types	Without
Contact Series	0.64

Housing Features

Housing Material	Nylon - GF35
Centerline (mm [in])	2.54 [0.100]
Mating Alignment	With
Mating Alignment Type	Keyed

Configuration Features

Number of Positions	52
Number of Rows	4
Strain Relief	Without

Industry Standards

RoHS/ELV Compliance 	ELV compliant
Lead Free Solder Processes 	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was ELV compliant
UL Flammability Rating	UL 94-HB

Identification Marking

Keying	A, E
--------	------

Environmental

Operating Temperature (°C [°F])	-40 - +125 [-40 - +257]
---------------------------------	-------------------------

Conditions for Usage

Applies To	Wire/Cable
For Use With	Receptacle: 1326042

Operation/Application

Application Use	Wire-to-Wire
Contact Transmits (Typical Application)	Signal

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Brand	TE Connectivity
Comment	Tested to 20mV @ 100mA

Related Products

Not quite the product
you're looking for?
[Find Similar Products](#)

[View Part in Product
Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TETe InvestorsNews RoomSupplier PortalCareersTerms & ConditionsPrivacy PolicyGlobal Accessibility Statement

Quick Links

Distributor InventoryProduct Cross ReferenceDocuments & DrawingsProduct Compliance Support CenterSite Map

Customer Support

Email or Chat With UsFind a Phone NumberKnowledge BaseManage Your Account

Keep Me Informed

