



2-Way Outlet Shapes, VG style 206-1-GWM250

Helashrink 200 Series, Article number: 402-06185



Images (3)

Downloads

Features

- Mechanical tension relief in cable harnesses

Certifications & Approvals



Application

Heat Shrinkable moulded shapes for use in Electrical and Electronic Cable Harness Applications

More products in this product group


[2-Way Outlet Shapes, VG style >](#)



Base Data

Application Tool	H5002 , H5004 , E4500
Colour	Black (BK)
Description Short (BMEcat) (max. 150 characters)	2-Way Outlet Shape VG-Style black, PO-X
GLOBAL PART DESCRIPTION	206-1-GWM250-PO-X-BK
Pack Cont.	1 pc.
Package Quantity per	pcs.
Product Family	Helashrink 200 Series
Product Group	2-Way Outlet Shapes, VG style
Variant	For 2-core cables

Product Dimensions



Flexibility	semi rigid
HW ± 30 %	1.5 mm
JW nom.	1 mm

JW/KW ± 30%	1 mm
JW/KW ± 30%	1 mm
P ± 10 %	41 mm
P ±10%=overall length	41 mm
R nom.	22 mm
R ± 10 %	19 mm
S nom.	19 mm
øH max. b	6 mm
øH min. a	13 mm
øJ max. b	3 mm
øJ min. a	7 mm
øJ/K max. b	3 mm
øJ/K min. a	7 mm
øK max. b	3 mm
øK min. a	7 mm

Material and Specifications



Adhesive	WM250
Dielectric Strength	15 kV/mm according to ASTM D2671
ELV compliant (Article 4 - 2)	YES
Flammability	ASTM D635
Hazardous good	No
Material	Polyolefin, cross-linked (PO-X)
Min. Shrink Temperature - °C	+135 °C
Operating Temperature - °C	-75 °C to +150 °C
Specifications	

Logistics and Packaging




More Information




ETIM 5.0	EC002464
ETIM 6.0	EC002464

Further information to 206-1-GWM250



Technical drawing
152035_1_9

 Download >



Moulded Shapes
Brochure 2016

Competences



Heat shrink tubing

You are looking for the heat shrink tubing meeting your application requirements best? The key factors to which we owe our success are the unique and quite specific properties of our heat shrink tubing.

[Heat Shrink Tubing >](#)

Accessories



H5002
391-50200
Electrical Hot Air Tool



H5004
391-50400
Electrical Hot Air Tool



E4500
391-90002
Gas powered Hot Air Tool

Similar products



203-1-B7
402-03001
2-Way Outlet Shapes,
VG style



203-1-B7P
402-03004
2-Way Outlet Shapes,
VG style



203-1-B7W21
402-03006
2-Way Outlet Shapes,
VG style



203-1-B7W8
402-03007
2-Way Outlet Shapes,
VG style



203-1-B7WM250
402-03008
2-Way Outlet Shapes,
VG style



203-1-B7PWM250
402-03051
2-Way Outlet Shapes,
VG style

[Show all >](#)

Stay in touch with us!



Global Company

About us
Worldwide
Philosophy
Environment & Quality
Corporate Social
Responsibility
Product Development
E-Business
ACADEMY
Careers
MADE FOR REAL

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors
Cable rods
Downlight covers
Cable jointing
Gel-filled cable joints

Markets & Industries

Automotive Industry
Solar plants
Wind turbines
Shipbuilding
Panel building
Rail industry
Food Industry
Chemical Industry
Aerospace Industry
Defence Industry

Media Centre

Videos
Product Catalogue
2018/2019
Automotive Catalogue
2016/2017
Connectivity Catalogues
2016/2017
Brochures
Software & Drivers
Helatag & Helafix
Templates
Manuals & Operating
Instructions

Cable Tie Guns
Connectivity Products
RFID tracking
Cable tie mounts
Thermal Transfer Printer
P-Clamp
Wiring ducts
Cable clips for edges
Cable management high
temperature
applications

Events

Update: 07/10/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

[I accept cookies](#)

[I refuse cookies](#)

[Privacy](#)

[Contact](#) [Terms of Service](#) [Imprint](#) [Privacy Policy](#)

[statement](#)