


Connector Location A

Connector Location B



Protection cap

Heat shrink tube


Protection cap

HARTING PushPull V4 2.0 SFP LC duplex, overmolded (IP65/67)

1x SC duplex (IP20)


X
male
(without protection cap)

Y
male
(without protection cap)



Loading Plan

A fiber 1 B
B fiber 2 A



- Temperature range: -40°C ... +85°C

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by COSTEA Costea		Inspected by 402676 Gross		Standardisation MUNTEANV Muntean		Date 2021-02-23	
Department HCS - RO		Title FO CA PP2-SCdx, 50µ, OM3, PUR		Type TB		Number 3361431XXX0005		State Final Release	
HARTING Customised Solutions		D-32339 Espelkamp		Doc-Key / ECM-Nr. 100677832/UGD/009/E 500000189720		Rev. E		Page 1/2	

	1	2	3	4	5	6	7	8
A								
B								
C	27	33614311000005	FO Breakout Cable, MM, 50/125µm, PUR, black, bend tolerant OM3	100				
	26	33614310900005		90				
	25	33614310800005		80				
	24	33614310700005		70				
	23	33614310600005		60				
	22	33614310500005		50				
	21	33614310450005		45				
	20	33614310400005		40				
	19	33614310350005		35				
D	18	33614310300005		30				
	17	33614310250005		25				
	16	33614310200005		20				
	15	33614310150005		15				
	14	33614310140005		14				
	13	33614310130005		13				
	12	33614310120005		12				
E	11	33614310110005		11				
	10	33614310100005		10				
	9	33614310090005		9				
	8	33614310080005		8				
	7	33614310070005		7				
	6	33614310060005		6				
	5	33614310050005		5				
F	4	33614310040005		4				
	3	33614310030005		3				
	2	33614310020005		2				
	1	33614310010005		1				
	Cont. no.	Part no.	Type of cable	Dim. a[m]				



All rights reserved

Department HCS - RO

All Dimensions in mm

Tech. Character.

Free size tol.

According to production drawing

Created by
COSTEA
Costea

Inspected by
402676
Gross

Standardisation
MUNTEANV
Muntean

Date
2021-02-23

State
Final Release

Title
FO CA PP2-SCdx, 50µ, OM3, PUR

Doc-Key / ECM-Nr.
100677832/UGD/009/E
500000189720

Type
TB

Number
3361431XXX0005

Rev.
E

Page
2/2

HARTING Customised Solutions

D-32339 Espelkamp