

BOARD-TO-BOARD HEADERS & RECEPTACLES



TE CONNECTIVITY (TE)
1FHP,64,50A/P,N,C,S10,12,13,15
 1.0mm FH | 1mm FH

1-120534-1
 TE Internal Number: 1-120534-1

5 of 6 EU RoHS/ELV Compliant
[Find Compliant Alternatives](#)

Connector Style **Plug**

Centerline **.63 mm [1 in]**

Stack Height (mm) **10, 12, 13, 15**

Stack Height (in) **.591**

Number of Positions **64**

Packaging Method **Tape & Reel**
[See All Features](#)

[Feedback](#)

Active

[PRODUCT DRAWING](#)
English

[3D PDF](#)

[See All Documentation](#)

North America

[GET SAMPLE](#)



[SAVE TO LIST](#)



About TE Connectivity Our Company Events TE News Center Careers Investors Corporate Responsibility Terms and Conditions of Sale	For Partners Distributors Suppliers	Customer Support Call Email Find Authorized Distributors Access Product Tools & Resources Share Feedback	CALL US LIVE CHAT	United States
--	---	---	--	-----------------------------------

CAD Files

[Customer View Model](#)
 2D_DXF.ZIP
 English

[Customer View Model](#)
 3D_IJGS.ZIP
 English

[Customer View Model](#)
 3D_STP.ZIP
 English

[3D PDF](#)
 PDF
 English

Product Specifications

Product Specification

[1.0 Mm Mezzanine Connectors](#)
 PDF
 English

COMPATIBLE

Products - 19 Results

[View All](#)

Compare 0/10

Relation Type

RELATIONSHIP

Mating Products

Used to identify Mating Parts

[See All Mating Products](#)

	<p>PRODUCT - MATING PRODUCTS</p> <p>Connectors - Board-to-Board Headers & Receptacles 1.0mm FH 1mm FH 1FHR, 64, 50A/P, N, C, S14, 15 - 1-120531-1 TE INTERNAL NUMBER: 1-120531-1</p> <p>Active</p>	<p>5 of 6 EU RoHS/ELV Compliant</p> <p>Connector Style Receptacle</p> <p>Centerline .63 mm</p> <p>Stack Height 14 mm, 15 mm</p> <p>Number of Positions 64</p> <p>Packaging Method Tape & Reel</p>	<input checked="" type="checkbox"/>
	<p>Quick View</p>		

RELATIONSHIP

Mating Products

Used to identify Mating Parts

[See All Mating Products](#)

	<p>PRODUCT - MATING PRODUCTS</p> <p>Connectors - Board-to-Board Headers & Receptacles 1.0mm FH 1mm FH 1FHR, 64, 50A/P, S, N, S14, 15 - 1-120524-1 TE INTERNAL NUMBER: 1-120524-1</p> <p>Active</p>	<p>5 of 6 EU RoHS/ELV Compliant</p> <p>Connector Style Receptacle</p> <p>Centerline .63 mm</p> <p>Stack Height 14 mm, 15 mm</p> <p>Number of Positions 64</p> <p>Packaging Method Tape & Reel</p>	<input checked="" type="checkbox"/>
	<p>Quick View</p>		

RELATIONSHIP

Mating Products

Used to identify Mating Parts

[See All Mating Products](#)

	<p>PRODUCT - MATING PRODUCTS</p> <p>Connectors - Board-to-Board Headers & Receptacles 1.0mm FH 1mm FH 1FHR, 64, 50A/S, N, C, S14, 15 - 1-5120531-1 TE INTERNAL NUMBER: 1-5120531-1</p> <p>Active</p>	<p>Always EU RoHS/ELV Compliant</p> <p>Connector Style Receptacle</p> <p>Centerline .63 mm</p> <p>Stack Height 14 mm, 15 mm</p> <p>Number of Positions 64</p> <p>Packaging Method Tape & Reel</p>	<input checked="" type="checkbox"/>
	<p>Quick View</p>		