



**Part Number :** [640031100](#)  
**Product Description :** Hand Crimp Tool  
**Series Number :** 207129  
**Status :** Active  
**Product Category :** Crimp Presses and Crimp Hand Tools  
**Engineering Number :** RHT-1751



## Documents & Resources

### Tooling Specifications

- [ATS-640031100-001.pdf](#)
- [TM-640160065-001.pdf](#)
- [TM-640160065CN-001.pdf](#)
- [TM-640160065SP-001.pdf](#)
- [TM-640160065IT-001.pdf](#)
- [TM-640160065JP-001.pdf](#)
- [TM-640160065KR-001.pdf](#)
- [TM-640160065MY-001.pdf](#)
- [TM-640160065PL-001.pdf](#)
- [TM-640160065RU-001.pdf](#)
- [TM-640160065SK-001.pdf](#)
- [TM-640160065TH-001.pdf](#)
- [TM-640160065VN-001.pdf](#)
- [TM-640160065TW-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)8585-DC

	(23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

**Part Details**

**General**

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822348637232
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized

	<p>distributors ("Molex Tooling").</p> <p>When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer.</p> <p>Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>
--	--

## Applicable Parts

Description	Part Number
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm <sup>2</sup> ) Wire, Box, Tab 2.79 x 0.51mm	<u>190160001</u>
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm <sup>2</sup> ) Wire, Box, Tab 2.79 x 0.81mm	<u>190160003</u>
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm <sup>2</sup> ) Wire, Box, Tab 4.75 x 0.51mm	<u>190160005</u>
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm <sup>2</sup> ) Wire, Box, Tab 4.75 x 0.81mm	<u>190160006</u>
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm <sup>2</sup> ) Wire, Box, Tab 6.35 x 0.81mm	<u>190160009</u>
Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm <sup>2</sup> ) Wire, Box, Tab 2.79 x 0.51mm	<u>190160035</u>
Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm <sup>2</sup> ) Wire, Box, Tab 2.79 x 0.81mm	<u>190160037</u>
Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm <sup>2</sup> ) Wire, Box, Tab 4.75 x 0.51mm	<u>190160039</u>

Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm <sup>2</sup> ) Wire, Box, Tab 4.75 x 0.81mm	<u>190160040</u>
Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm <sup>2</sup> ) Wire, Box, Tab 6.35 x 0.81mm	<u>190160111</u>
Krimptite Snap Receptacle, for 22-18 AWG Wire, Box, 16.26mm Length	<u>190370002</u>
Krimptite Snap Receptacle, for 16-14 AWG Wire, Box, 16.26mm Length	<u>190370004</u>
Krimptite Snap Receptacle, for 16-14 AWG Wire, Box, 17.80mm Length	<u>190370006</u>
Krimptite Snap Receptacle, for 22-18 AWG Wire, Box, 17.80mm Length	<u>190370015</u>
Krimptite Quick Disconnect, Female, Steel, 483°C (900° F), 16-14 AWG, Tab 6.35mm	<u>192030390</u>
Quixon Quick Disconnect, Krimptite Style, Female, Un-insulated, 20-18 AWG, Loose	<u>192730007</u>
Quixon Quick Disconnect, Krimptite Style, Female, Un-insulated, 16-14 AWG, Loose	<u>192730008</u>

---

This document was generated on Sep 11, 2025