

SKINDICHT® SM-M

SKINDICHT® SM-M, metric counter nuts for through-holes on thin-walled housings

Info

Also available as lead-free version - the lead-free articles end on LF after the article number



Good chemical resistance



Mechanical resistance

Application range

Used when a gland has to be countered, or in through-holes on thin-walled housings

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000940

ETIM 6.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-60°C to +200°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® SM-M

Article number	Article designation / size	Thickness (mm)	SW wrench size mm	Outer Ø (mm)	Pieces / PU
SKINDICHT® SM-M					
52102998	M 6 x 1	3.2	10	11.1	50
52102997	M 8 x 1	4.0	13	14.4	50
52102999	M 10 x 1	5.0	17	19.1	50
52103000	M 12 x 1,5	3.0	15	16.5	100
52103010	M 16 x 1,5	3.0	19	20.9	100
52103020	M 20 x 1,5	3.5	24	26.4	100
52103030	M 25 x 1,5	4.0	30	33.0	100
52103040	M 32 x 1,5	4.0	36	39.6	100
52103050	M 40 x 1,5	5.0	46	50.6	50
52103060	M 50 x 1,5	5.0	60	65.0	50
52103070	M 63 x 1,5	5.0	70	77.0	25
52103071	M 75 x 1,5	8.0	85	95.0	1
52103072	M 90 x 2	10.0	102	114.0	1
52103073	M 110 x 2	12.0	124	135.0	1
SKINDICHT® SM-M - Lead-free brass version					
52103000LF	M 12 x 1,5	3.0	15	16.5	100
52103010LF	M 16 x 1,5	3.0	19	20.9	100
52103020LF	M 20 x 1,5	3.5	24	26.4	100
52103030LF	M 25 x 1,5	4.0	30	33.0	100
52103040LF	M 32 x 1,5	4.0	36	39.6	100
52103050LF	M 40 x 1,5	5.0	46	50.6	50
52103060LF	M 50 x 1,5	5.0	60	65.0	50
52103070LF	M 63 x 1,5	5.0	70	77.0	25

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16