



**Part Number :** [734151122](#)  
**Product Description :** MMCX Plug, Right-Angle, Crimp, RG-174, RG-188 and RG-316 Cable, Brass Body, Gold (Au) Plated, One Piece Per Bag, 50 Ohms  
**Series Number :** 73414  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



Documents & Resources

Drawings

[734151122 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                                 |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                               |
| REACH SVHC         | Contains Lead per D(2025)4165-DC<br>(25 June 2025)                                                           |
| EU RoHS            | Compliant with Exemption 6(c) per<br>EU 2015/863                                                             |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

|              |                                                                                                                          |
|--------------|--------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                   |
| Category     | RF / Coaxial Connectors                                                                                                  |
| Series       | 73414                                                                                                                    |
| Description  | MMCX Plug, Right-Angle, Crimp, RG-174, RG-188 and RG-316 Cable, Brass Body, Gold (Au) Plated, One Piece Per Bag, 50 Ohms |
| Application  | RF                                                                                                                       |
| Product Name | MMCX                                                                                                                     |
| Style        | Cable                                                                                                                    |
| Type         | Microminiature                                                                                                           |
| UPC          | 800756723389                                                                                                             |

### Electrical

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 6 GHz                       |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 170 Vrms@Sea Level |

### Physical

|                       |                |
|-----------------------|----------------|
| Cable Attachment      | Crimp          |
| Gender                | Plug           |
| Keying to Mating Part | N/A            |
| Net Weight            | 0.768/g        |
| Orientation           | Right Angle    |
| Packaging Type        | Individual Bag |

|                    |                                 |
|--------------------|---------------------------------|
| Panel Mount        | No                              |
| Panel Mount Method | N/A                             |
| PCB Mounting       | N/A                             |
| Reverse Polar      | No                              |
| Wire/Cable Type    | LMR-100, RG-174, RG-188, RG-316 |

---

This document was generated on Sep 26, 2025