





DIMENSION TABLE :-

SR. NO.	MIL PART. NO. (FOR CADMIUM)	MIL PART. NO. (FOR NICKEL)	SHELL SIZE	'A'	'B'	'C'	'D'	'E'	'F'	'G'	'H'	'L' ± 0.80
1	M85049/48-2-1F	M85049/48-2-1N	1	31.06 30.30	13.08 12.32	25.12 24.87	10.31	17.17 16.41	3.56 2.79	26.95 25.43	9.12 8.36	9.53
2	M85049/48-2-2F	M85049/48-2-2N	2	39.26 38.51	13.08 12.32	33.45 33.20	10.31	25.37 24.61	3.56 2.79	26.95 25.43	9.12 8.36	9.53
3	M85049/48-2-3F	M85049/48-2-3N	3	53.16 52.40	13.08 12.32	47.17 46.91	15.06	38.86 38.10	5.13 4.37	27.74 26.21	9.12 8.36	9.53
4	M85049/48-2-4F	M85049/48-2-4N	4	69.42 68.66	13.08 12.32	63.63 63.37	18.25	55.52 54.76	6.73 5.97	27.74 26.21	9.12 8.36	12.70
5	M85049/48-2-5F	M85049/48-2-5N	5	67.06 66.29	15.85 15.09	61.24 60.99	20.62	53.54 52.78	8.31 7.54	27.74 26.21	11.51 10.74	15.88

5	21/08/14
4	20/08/14
3	20/03/13
2	18/03/13
Issue No.	Rev. Date.

ALL DIM'S ARE IN MM

D-SUB RECTANGULAR BACKSHELL
(09 TO 50 PIN) WITH T-CLAMP

Scale
2:1

Dwg. No.
C-80414

Drawn by. *Ramesh*
Date 15/03/13

Amphenol
Amphenol Interconnect India Pvt. Ltd.
PUNE-411026

ORDERING INFORMATION:—

M85049 / 48 - 2 - 1 F

SERIES NO. _____

BACKSHELL _____

FIGURE _____

SHELL SIZE (1,2,3,4,5) _____

FINISH _____

MATERIAL & FINISH :


1. SHELL — STEEL AS PER NFA 37-501
2. CLAMP — STEEL AS PER NFA 37-501
3. SCREW — SS 303 OR 304
4. NYLOC NUT — SS 303 OR 304

FINISH :—

1. F — CADMIUM PLATING WITH YELLOW PASSIVATION
2. N — ELECTROLESS NICKEL PLATING.

NOTES:—

1. SCREW & NYLOCK NUT WILL BE SUPPLIED LOOSE WITH BACKSHELL.



ALL DIM'S ARE IN MM

D-SUB RECTANGULAR BACKSHELL
(09 TO 50 PIN) WITH T-CLAMP

Scale
2:1

Dwg. No.

C-80414

Drawn by.

Ramesh

Date

15/03/13

Amphenol

Amphenol Interconnect India Pvt. Ltd.

PUNE-411026