



Part Number : [503518000](#)

Product Description : 2.50mm Pitch, Mini-Lock Female Crimp Terminal, Tin Plating, 28-22 AWG, Reel

Series Number : 50351

Status : Not Recommended For New Design

Product Category : Crimp Terminals

Packaging Alternative : [503518100](#) (Bag)



Documents and Resources

Specifications

[503519200-SPK-200.pdf](#)

[511030000-PS-000.pdf](#)

[PS-51103-001-001.pdf](#)

[PS-51103-002-001.pdf](#)

[PS-51103-005-001.pdf](#)

[PS-51103-006-001.pdf](#)

[PS-51103-026-001.pdf](#)


[PS-51103-027-001.pdf](#)

[PS-51103-028-001.pdf](#)

[PS-51198-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Crimp Terminals
Series	50351
Description	2.50mm Pitch, Mini-Lock Female Crimp Terminal, Tin Plating, 28-22 AWG, Reel
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	Mini-Lock
UPC	800753576162

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	59.840/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.15-1.80mm
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Lock Single Row Receptacle Housings	<u>51103</u>

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Mini-Lock Terminals, 28-22 AWG	<u>638118100</u>
Extraction and Activation Tool	<u>638132700</u>
T2 Terminator Die	<u>638505100</u>
FineAdjust Applicator for 2.50mm Pitch Crimp Terminals, 28-22 AWG Wire with Insulation Diameter 1.20-1.65mm for IPC Class 2	<u>638605100</u>

This document was generated on May 20, 2026