

Connectors > Rectangular Connectors > Rectangular Contact Inserts

1-1195304-5 ACTIVE

Rectangular Contact Inserts, Insert for Contacts, Socket, Wire-to-Wire, 5 Position, Sealable, 16 AWG Wire Size, 1.5 mm² Wire Size, 1.5 A



RAYCHEM

TE Internal #: **674339-000**
TE Internal Description: **MTCP-116-05S2**
Mil-Spec: **B: MTCP116-05S2**

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **5**
Centerline (Pitch) : **1.27 mm [.05 in]**

Add to List | Similar Products | Digital Datasheet

Compatible Parts & Tooling

Documents	Features	Product Compliance
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.		
Product Type Features	Rectangular Connector Insert Type : Insert for Contacts Connector System : Wire-to-Wire Sealable : Yes Connector & Contact Terminates To : Wire & Cable	
Configuration Features	Number of Positions : 5	
Body Features	Primary Product Color : Black Primary Product Material : High Grade Polyarylene Thermoplastic Seal Type : Grommet Seal	
Contact Features	Contact Type : Socket Contact Current Rating (Max) (A): 1.5	
Mechanical Attachment	Polarization Code : A/B Connector Mounting Type : Panel Mount	
Housing Features	Centerline (Pitch) : 1.27 mm [.05 in]	
Dimensions	Wire Size (AWG): 16 Wire Size (mm ²): 1.5	
Usage Conditions	Operating Temperature Range : -65 – 125 °C [-85 – 257 °F]	
Operation/Application	Compatible With Connector Shell Size : 50.8 [2.0]	

Compatible Parts

ACCESSORY

CTA-0078

CTA-0078

From: \$12.790

In-Stock

VIEW PRODUCT

Filter By Specification

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

RECTANGULAR CONTACT INSERTS

1-1195304-5

Rectangular Contact Inserts, Insert for Contacts, Socket, Wire-to-Wire, 5...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **5**
Centerline (Pitch) : **1.27 mm**

TOP RESULTS

RECTANGULAR CONTACT INSERTS

2-1191312-8

Rectangular Contact Inserts, Insert for Contacts, Socket, Wire-to-Wire, 5...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **5**
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS

1-1196320-6

Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 5...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : **5**
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS

MTCPK1PJC06S

Rectangular Contact Inserts, Socket, Wire-to-Wire, 5 Position, Sealable, 16...

Non-Stocked

Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **5**
Centerline (Pitch) : **1.27 mm**
Sealable : **Yes**

Customers Also Bought

TE Part #: **38941-22L**
Pin Contact, Gold, Size 22
Contact Size, 28 – 22 AWG...

\$0.260 per unit

Inventory: In-Stock

Add To Cart

TE Part #: **MTCP-122-20PQ1**
Rectangular Contact Inserts, Insert for Contacts, Pin...

View Product

TE Part #: **MTCP-122-20PQ2**
Rectangular Contact Inserts, Insert for Contacts, Pin...

View Product

TE Part #: **MTCP-122-20PQ**
Rectangular Contact Inserts, Insert for Contacts, Pin...

View Product

TE Part #: **MTC100Q-SH2-P22**
Standard Rectangular Connectors, Housing Kit...

View Product

TE Par **P22**
Standi Conne

Vie

Contact Our Team – 24/7 Support

+1 800 522 6752

Live Chat

See Support Details

Connect With Us



Access Partner Information

Distributors

Suppliers

Supplier Diversity

Get Answers Now

Authorized Distributors & Resellers

Product FAQs

Samples FAQs

TE Store FAQs

Terms and Conditions of Sale

Samples Terms and Conditions

Select Your Preferences

Language

English (EN)

Ship to

United States (\$USD)