


# RIBBON CABLE CONNECTORS



TE CONNECTIVITY (TE)

IDC LOW PRO HDR 10P RA SHT LAT

AMP-LATCH | Low Profile Headers

2-1761609-3

TE Internal Number: 2-1761609-3

Always EU RoHS/ELV Compliant

Centerline **2.54 mm [ .1 in ]**

PCB Mount Retention **Without**

PCB Mounting Orientation **Right Angle**

Termination Method to PC Board **Through Hole**

Shrouded **Yes**

[See All Features](#)

Active

PRODUCT DRAWING  
English

3D PDF

[See All Documentation](#)

Feedback

North America

GET SAMPLE

SAVE TO LIST

DISTRIBUTOR	QUANTITY	DATE AS OF
-------------	----------	------------

About TE Connectivity

For Partners

Customer Support

CALL US

LIVE CHAT

United States

Our Company

Events

TE News Center

Careers

Investors

Corporate Responsibility

Terms and Conditions of Sale

Distributors

Suppliers







Call

Email

Find Authorized Distributors

Access Product Tools & Resources

Share Feedback

© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

Terms of Use

Privacy

Cookie Policy

Accessibility

Site Map

## CAD Files

[Customer View Model](#)  
3D\_STR.ZIP  
English

[Customer View Model](#)  
2D\_DXF.ZIP  
English

[3D PDF](#)  
PDF  
3D

[Customer View Model](#)  
3D\_IGS.ZIP  
English

## Product Specifications

Product Specification

[AMP-LATCH And IDC Header Connectors, .100 X .100 Inch Grid](#)  
PDF  
English

## Product Environmental Compliance

TE Material Declaration

[MD\\_2-1761609-3\\_052220151624\\_dmtec](#)  
PDF  
English

## COMPATIBLE

Products - 8 Results

[View All](#) [Compare 0/10](#)

Relation Type


RELATIONSHIP

Mating Products

Used to identify Mating Parts

[See All Mating Products](#)

PRODUCT - MATING PRODUCTS



Connectors - Ribbon Cable Connectors

AMP-LATCH | AMP-LATCH - NOVO

10 NOVO MIL 15DP,  
LEAD FREE - 1658620-1

TE INTERNAL NUMBER: 1658620-1

Active

Always EU RoHS/ELV Compliant

Centerline **2.54 mm**

PCB Mount Retention **Without**

PCB Mounting Orientation **Vertical**

Termination Method to PC Board **Through Hole - Solder**

Termination Method to Wire/Cable **Insulation Displacement Crimp (IDC)**

Quick View


RELATIONSHIP

Mating Products

Used to identify Mating Parts

[See All Mating Products](#)

PRODUCT - MATING PRODUCTS



Connectors - Ribbon Cable Connectors

I AMP-LATCH - NOVO

609-1000MLF FEM SCKT,  
LEAD FREE - 1658526-3

TE INTERNAL NUMBER: 1658526-3

Active

Always EU RoHS/ELV Compliant

Number of Positions **10**

Connector Style **Receptacle**

Quick View


RELATIONSHIP

Mating Products

Used to identify Mating Parts

[See All Mating Products](#)

PRODUCT - MATING PRODUCTS



Connectors - Ribbon Cable Connectors

I AMP-LATCH - NOVO

609-1030LF FEM SOCKET,  
LEAD FREE - 1658526-4

TE INTERNAL NUMBER: 1658526-4

Active

Always EU RoHS/ELV Compliant

Number of Positions **10**

Connector Style **Receptacle**

Quick View

Downloaded from Arrow.com