Data Sheet | Item Number: 890-523

Shield connecting plate; 3-pole; for sockets and plugs; silver-colored

https://www.wago.com/890-523



Color: silver-colored

Shield termination *WINSTA*® MINI 3-pole

Thanks to the shield termination from the *WINSTA*® MINI product line, straightforward electrical installation is ensured. You can rely on the level of quality of-WINSTA® components from WAGO for your electrical installation accessories too. Thanks to its particularly minimal dimensions, our *WINSTA*® MINI Pluggable Connection System with Push-in CAGE CLAMP® spring pressure connection technology is specifically suitable in very tight spaces, i.e., for connections when very little room is available.

Lower costs through fast commissioning and elimination of service expenses – solutions from *WINSTA*® MINI

WINSTA® is the pluggable connection system that is perfectly tailored to the strict requirements of electrical installation. It offers fast, secure and, above all, er-ror-free installation of components and cables. Choose durability and quality – with protection against mismating from WAGO makes the electrical installation of electrical components visibly easier.

- easy tool-free operation, a wide range of coding options
- quick replacement of defective units during ongoing operation

Notes

General safety information	**NOTICE: Observe installation and safety instructions!** 1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100). 2. Do not install while energized or under load. 3. Use only for its intended purpose. 4. Observe applicable national regulations, standards and directives. 5. Observe the technical specifications of the products. 6. Ensure correct polarity assignment. 7. Do not use damaged or contaminated components. 8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters. 9. Insert conductors up to the stop. 10. Use only with locking lever and strain relief. 11. Use original accessories only. **To be sold only with installation instructions!**

Downloaded from Arrow.com.

Connection Data

Connection 1

Pole number	3

Physical data

Width	9.8 mm / 0.386 inches
Height	3.5 mm / 0.138 inches
Depth	43.5 mm / 1.713 inches

Mechanical data

Suitable	for socket and plug

Material data

Note (material data)	Information on material specifications can be found here
Color	silver-colored
Flammability class per UL94	V0
Weight	1.1 g
Material	Copper (SE Cu); special tin coating

Environmental requirements

Processing temperature	-5 … +40 °C
Continuous operating temperature	-35 … +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

Product Group	20 (Winsta)
PU (SPU)	50 (1) pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454730420
Customs tariff number	74099000000

Product Classification

UNSPSC	39121421
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION

Downloaded from Arrow.com.

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 890-523

Documentation

Bid Text

890-523	19.02.2019	xml 2.56 KB
890-523	26.11.2014	doc 22.50 KB

CAD/CAE-Data

CAD data

2D/3D Models 890-523

CAE data

WSCAD Universe 890-523

Downloaded from Arrow.com.