Data sheet

# M-D-STRIPAX AWG 26+28

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

## General ordering data

| | |
|---|---|
| Version | Tools, Stripping and cutting tool |
| Order No. | 9003710000 |
| Type | M-D-STRIPAX AWG 26+28 |
| GTIN (EAN) | 4008190034184 |
| Qty. | 1 items |
| Delivery status | Discontinued |
| Available until | 2022-03-01T00:00:00+01:00 |
| Alternative product | MEHA KP RT M-D-SPX |



Downloaded from Arrow.com.

# Data sheet

## M-D-STRIPAX AWG 26+28

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 16 mm | Depth (inches) | 0.6299 inch |
| Height | 135 mm | Height (inches) | 5.3149 inch |
| Width | 82 mm | Width (inches) | 3.2283 inch |
| Net weight | 97.28 g | | |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0 |

### Technical data

| | |
|---|---|
| Description of article | Stripping tool for up to AWG 24, for PTFE |

### Stripping tools

| | | | |
|---|---|---|---|
| Cable type | Conductor with custom insulation | Max. conductor diameter | 0.5 mm |
| Min. conductor diameter | 0.3 mm | Stripping range AWG, max. | 24 AWG |
| Stripping range AWG, min. | 28 AWG | Stripping length, max. | 7 mm |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC002109 | ETIM 9.0 | EC002109 |
| ETIM 10.0 | EC002109 | ECLASS 14.0 | 21-04-37-06 |
| ECLASS 15.0 | 21-04-37-06 | | |



Downloaded from Arrow.com.

# M-D-STRIPAX AWG 26+28

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

### Example of use





Downloaded from Arrow.com.

# M-D-STRIPAX AWG 26+28

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Accessories / replacement parts



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

### General ordering data

| | | |
|---|---|---|
| Type | MEHA KP GE M-D-SPX | Version |
| Order No. | 9003600000 | Accessories, Set of cutters |
| GTIN (EAN) | 4008190140274 | |
| Qty. | 1 ST | |
| Type | MEHA KP RT M-D-SPX | Version |
| Order No. | 9003610000 | Accessories, Set of cutters |
| GTIN (EAN) | 4008190058272 | |
| Qty. | 1 ST | |
| Type | MEHA KP GN M-D-SPX | Version |
| Order No. | 9003620000 | Accessories, Set of cutters |
| GTIN (EAN) | 4008190130527 | |
| Qty. | 1 ST | |
| Type | MEHA KP BL M-D-SPX | Version |
| Order No. | 9003630000 | Accessories, Set of cutters |
| GTIN (EAN) | 4008190094256 | |
| Qty. | 1 ST | |
| Type | MEHA KP SW M-D-SPX | Version |
| Order No. | 9003640000 | Accessories, Set of cutters |
| GTIN (EAN) | 4008190020507 | |
| Qty. | 1 ST | |
| Type | MEHA KP WS M-D-SPX | Version |
| Order No. | 9006970000 | Accessories, Set of cutters |
| GTIN (EAN) | 4032248363711 | |
| Qty. | 1 ST | |



Downloaded from Arrow.com.