molex



Part Number : 08650115
Product Description : KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au) Plated
Series Number : 2478
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 2478-3-(555)L
Packaging Alternative : 08650114 (Reel)

Documents and Resources

Drawings

008650115_sd.pdf

PK-2759-001-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-08-50-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	2478
Description	KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au) Plated
Application	Power, Wire-to-Board
Product Name	KK 396,KK 508
UPC	800754227230

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.150/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.

Downloaded from Arrow.com.

Wire Size (AWG)	18, 20, 22, 24
Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	2139
KK 5.08mm Pitch Single Row Crimp Housings	3001
KK 3.96mm Single Row Crimp Housings	3069
5.08mm Pitch KK Crimp Housings	91813
KK 3.96mm Crimp Housings	41695

Application Tooling

Global

Description	Part Number
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	11030016
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 24-18 AWG	638279500

Downloaded from Arrow.com.