

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUBLICATED NOR MADE AVAILABLE TO A THIRD PARTY,
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.

RoHS compliant
by exemption





1731121157	F-GSCH1/5-3858	Brass (nonmagnetic)	tin plated (nonmagnetic)	1	2	-	1
1731121344	F62M033S253+S	Steel (Lead free) 2)	zinc plated 1)	1	-	-	-
1731120561	F-GSCH1/5-K127		zinc plated 1)	1	2	1	1
1731121166	F-GSCH1/5-K127SSN	Steel	tin plated	1	2	1	1
1731120586	F-GSCH1/5-K127SN		tin plated	1	2	1	1
1731121343	F62M033S245+S		tin plated	1	-	-	-
1731121189	F-GSCH1/5-K959		zinc plated 1)	1	2	1	1 (HEX 5)
Material Number	*FCT Part Number*	*Material*	*Surface*	*Screw (pc.)*	*Washer (pc.)*	*Spring Washer (pc.)*	*Nut (pc.)*

Generally twice a material number respectively FCT part number is needed per connector.

Packaging specification: 1731120003-PK

1) With tension control fluid

2) RoHS compliant

FUNCTIONAL SYMBOLS
F = 0
F = 0
F = 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS: mm
SCALE: 2:1
MEASUREMENTS WITHOUT TOLERANCE ACC. TO: ISO 2768-mK

CURRENT REVISION
DRWN: DRAWN BY mteubel 21-11-2025
APPR: APPR BY mteubel 21-11-2025

INITIAL REVISION
DRWN: DRAWN BY Denzinger 01-07-2002
APPR: APPR BY schref 01-07-2002

7 24420
REV. CH.-NO.

REPLACEMENT FOR:

FIRST ANGLE PROJECTION

DRAWING: A4-SIZE

molex

FCT Female Screw Lock
F-GSCH1/5-K127 /-K959 / -3858

PRODUCT CUSTOMER DRAWING

MATERIAL NUMBER: see table
REVISION: 7

DOCUMENT NUMBER: F62M033_D
CUSTOMER: GENERAL MARKET
SHEET NUMBER: 1 OF 1

Downloaded from Arrow.com.