



Part Number : [08550129](#)

Product Description : KK High Pressure Crimp Terminal, Female, 30-24 AWG, Brass, 0.38µm Selective Gold (Au) Plating, Bag


Series Number : 7879

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 7879-1(P208)L

Packaging Alternative : [08550124](#) (Reel)



Documents and Resources

Drawings

[008550129 sd.pdf](#)

[PK-2759-001-001.pdf](#)

[PK-2759-002-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-7879-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	7879
Description	KK High Pressure Crimp Terminal, Female, 30-24 AWG, Brass, 0.38µm Selective Gold (Au) Plating, Bag
Application	Signal, Wire-to-Board
Product Name	KK High Pressure
UPC	800754226523

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.117/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size (AWG)	24, 26, 28, 30
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Extraction Tool for KK 2.54mm Terminals, 30-22 AWG	<u>11030022</u>
Insertion Tool for KK 2.54mm Terminals, 30-22 AWG	<u>638120000</u>
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 28-22 AWG	<u>638190800</u>

This document was generated on May 19, 2026