
BURNDY

K2C34B1, SERVIT POST Mechanical Connector, 2 Cables to Flat



By Burndy
Catalog # K2C34B1

SERVIT POST™ Mechanical Connector, 2 Cables to Flat

Features

- SERVIT POST mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - Copper Str Size Range	3/0 AWG-500 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	60.5 mm
Dimension - Height inch	2.38 in
Dimension - Height fraction	2-3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.85 in
Dimension - L Length Overall mm	104.6 mm
Dimension - Nut Width inch	2.00 in
Dimension - Threads per inch	10
Dimension - Bolt Size fraction	3/4
Dimension - Body Width inch	1.62 in
Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.49 in
Dimension - D inch	1.75 in
Dimension - Length Overall inch	4.12 in

Force Related

Stud Installation Torque inch pounds	1050 LBS/in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Bar/Flat
Trade Name	SERVIT POST™
Plated	No
Product Type	Mechanical
UPC	781810257753
Type	KC and K2C Series
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810257753
UPC 14 Digit GTIN	00781810257753

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.