
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION JAN ,2008.
© COPYRIGHT 2008 TE Connectivity Ltd. ALL RIGHTS RESERVED.


REVISIONS
変更

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | D1 | REVISED PER ECR-21-103336 | 21MAY2021 | SC | D.Z |

△1 取付穴寸法
2 適応基板厚：1.6 t
△3 かん合相手製品型番：
プラグハウジング：SEE TABLE
△4 青色については色むらがでる可能性があります。


△1 RECOMMENDED P.C.B LAY OUT
2 APPLICABLE P.C.B. THICKNESS: 1.6
△3 MATING CONN. P/N
PLUG HOUSING: SEE TABLE
△4 UNEVEN COLORING MAY COME OUT OF BLUE.





| | | |
|---|---|---|
| ② | ヘッダーハウジング (HEADER HOSING) | 6/6ナイロンガラス強化 (6/6 NYLON GRASS FILLED) |
| ① | タブ (TAB) | 錫めっき仕様 銅合金 (COPPER ALLOY TIN PLATED) |
| NO. | 名称 (NAME) | 材料 (MATERIAL) |

KEYING TYPE




| パンチ加工 (PUNCHED HOLE) | 1.25 |
|---|---|
| ドリル加工 (DRILLED HOLE) | 1.4 |
| | A 寸法 |

プリント基板推奨穴加工寸法
△1




THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位： 粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差

| | |
|---|---|
| 0 PLC | ± 0.3 |
| 1 PLC | ± 0.3 |
| 2 PLC | ± 0.3 |
| 3 PLC | ± 0.2 |
| 4 PLC | ± – |
| ANGLES | ±2° |

MATERIAL 材料: SEE TABLE
FINISH 仕上:
WEIGHT:

| | | |
|---|---|---|
| DWN | LILY LIU | 29JAN2008 |
| CHK | A.OISHI | 29JAN2008 |
| APVD | S.MANABE | 29JAN2008 |
| PRODUCT SPEC 製品規格 | 108-5990 | |
| APPLICATION SPEC 取付適用規格 | | |

TE Connectivity Ltd.

NAME 名称: GRACE INERTIA CONNECTOR 7.92MM PITCH HEADER ASSEMBLY 2P

| SIZE | CAGE CODE | DRAWING NO 番号 | RESTRICTED TO |
|---|---|---|---|
| A3 | 00779 | C-1747052 | — |

CUSTOMER DRAWING | SCALE 尺度 3:1 | SHEET 1 OF 2 | REV D1



Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION JAN ,2008.
© COPYRIGHT 2008 TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS
変更

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | – | SEE SHEET 1 | – | — | — |

| | | | | | |
|---|---|---|---|---|---|
| 3−1747050−5 | キンク有 WITH KINK | TYPE D | 緑色 GREEN | 2極 2POS | 3−1747052−5 |
| 3−1747050−4 | キンク有 WITH KINK | TYPE D | 黄色 YELLOW | 2極 2POS | 3−1747052−4 |
| 3−1747050−3 | キンク有 WITH KINK | TYPE D | 青色 BLUE 4 | 2極 2POS | 3−1747052−3 |
| 3−1747050−2 | キンク有 WITH KINK | TYPE D | 赤色 RED | 2極 2POS | 3−1747052−2 |
| 3−1747050−1 | キンク有 WITH KINK | TYPE D | 自然色 NATURAL | 2極 2POS | 3−1747052−1 |
| 2−1747050−5 | キンク有 WITH KINK | TYPE C | 緑色 GREEN | 2極 2POS | 2−1747052−5 |
| 2−1747050−4 | キンク有 WITH KINK | TYPE C | 黄色 YELLOW | 2極 2POS | 2−1747052−4 |
| 2−1747050−3 | キンク有 WITH KINK | TYPE C | 青色 BLUE 4 | 2極 2POS | 2−1747052−3 |
| 2−1747050−2 | キンク有 WITH KINK | TYPE C | 赤色 RED | 2極 2POS | 2−1747052−2 |
| 2−1747050−1 | キンク有 WITH KINK | TYPE C | 自然色 NATURAL | 2極 2POS | 2−1747052−1 |
| 1−1747050−5 | キンク有 WITH KINK | TYPE B | 緑色 GREEN | 2極 2POS | 1−1747052−5 |
| 1−1747050−4 | キンク有 WITH KINK | TYPE B | 黄色 YELLOW | 2極 2POS | 1−1747052−4 |
| 1−1747050−3 | キンク有 WITH KINK | TYPE B | 青色 BLUE 4 | 2極 2POS | 1−1747052−3 |
| 1−1747050−2 | キンク有 WITH KINK | TYPE B | 赤色 RED | 2極 2POS | 1−1747052−2 |
| 1−1747050−1 | キンク有 WITH KINK | TYPE B | 自然色 NATURAL | 2極 2POS | 1−1747052−1 |
| 1747050−6 | キンク有 WITH KINK | TYPE A | 黒色 BLACK | 2極 2POS | 1747052−6 |
| 1747050−5 | キンク有 WITH KINK | TYPE A | 緑色 GREEN | 2極 2POS | 1747052−5 |
| 1747050−4 | キンク有 WITH KINK | TYPE A | 黄色 YELLOW | 2極 2POS | 1747052−4 |
| 1747050−3 | キンク有 WITH KINK | TYPE A | 青色 BLUE 4 | 2極 2POS | 1747052−3 |
| 1747050−2 | キンク有 WITH KINK | TYPE A | 赤色 RED | 2極 2POS | 1747052−2 |
| 1747050−1 | キンク有 WITH KINK | TYPE A | 自然色 NATURAL | 2極 2POS | 1747052−1 |
| かん合相手(プラグ) P/N MATING CONN. P/N 3 | キンク有無 WITH/WITHOUT KINK | キーイングタイプ TYPE OF KEYING | 色 COLOR | 極数 POS | 型番 PART NO. |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位： 粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差

| | |
|---|---|
| 0 PLC | ± 0.3 |
| 1 PLC | ± 0.3 |
| 2 PLC | ± 0.3 |
| 3 PLC | ± 0.2 |
| 4 PLC | ± – |
| ANGLES | ± 2° |

MATERIAL 材料: SEE TABLE

FINISH 仕上:

DWN LILY LIU 29JAN2008
CHK A.OISHI 29JAN2008
APVD S.MANABE 29JAN2008
PRODUCT SPEC 製品規格: 108−5990
APPLICATION SPEC 取付適用規格:
WEIGHT:

TE Connectivity Ltd.

NAME 名称: GRACE INERTIA CONNECTOR 7.92MM PITCH HEADER ASSEMBLY 2P

| SIZE | CAGE CODE | DRAWING NO 番号 | RESTRICTED TO |
|---|---|---|---|
| A3 | 00779 | C−1747052 | — |

CUSTOMER DRAWING

| SCALE 尺度 | SHEET | REV |
|---|---|---|
| NTS | 2 OF 2 | D1 |



Downloaded from Arrow.com.