molex



**Part Number :** 369220801
**Product Description :** Ditto-to-Ditto Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, 100.00mm Length, 8 Circuits, Black
**Series Number :** 36922
**Status :** Obsolete
**Product Category :** Power and Signal Cable Assemblies

Obsolete

## Documents and Resources

### Drawings

369220801_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Obsolete |
| Category | Power and Signal Cable Assemblies |
| Series | 36922 |
| Description | Ditto-to-Ditto Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, 100.00mm Length, 8 Circuits, Black |
| Application | Power, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Ditto-to-Ditto |
| Product Name | Ditto |
| Type | Discrete Wire Assembly |
| UPC | 193264209057 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 4.2A |
| Voltage - Maximum | 300V AC/DC |

### Physical

| | |
|---|---|
| Cable Length | 100.00mm |
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | Black |
| Gender | Hermaphroditic-Hermaphroditic |
| Lock to Mating Part | Yes |
| Material - Metal | Tin Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |

Obsolete

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Resin | Nylon |
| Net Weight | 13.528/g |
| Number of Rows | 1 |
| Overmolded | No |
| Packaging Type | Bag |
| Pitch - Mating Interface | 3.00mm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 1061 |
| Wire Size (AWG) | 20 |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Ditto Hermaphroditic Crimp Housings | 150170 |

This document was generated on Apr 12, 2026

Obsolete

Downloaded from Arrow.com.