

Type H-WZ heavy duty, with Z-rail

SCHROFF



Other Views



Catalog Number: 34560-928

Back To Product

- For directly mounting connectors complying with EN 60603 (DIN 41612)
- < 28 HP not printed
- Al extrusion, anodised finish, conductive contact surface, with HP markings
- With Z-rail for high mechanical load (H-WZ)

Product family:

- RatiopacPRO
- PropacPRO
- CompacPRO
- EuropacPRO

Note:

Delivery is in standard pack multiples. Pricing is per individual item

Type:

Individual Components

Individual Component Type:

Horizontal Rails & Accessories

Standard pack quantity (SPQ):

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

Description:

Type H-MZ



Select product specifications before modifying or adding to project list or requesting a quote.

Length-mm-defining

[Clear Selection](#)

Quantity

Add Item to Project List +

Documents



Shock and vibration test according to IEC 48/IEC 61587



Shock and vibration test according to Deutsche Bundesbahn standards



Seismic test

Links



Native CAD files

Technical Data




Length mm	147.32
Qty	1 piece (SPQ 10)
Delivery is exclusively made in Standard Pack Quantity (SPQ)	10
Material	Aluminium extrusion
Finish	Anodised, conductive contact surfaces
Description	Horizontal rail
Description	For direct

connectors in
accordance
with EN
60603-2 (DIN
41612)

Delivery Comprises:

Item	Quantity	Description
1	1	Horizontal rail, Al-Profile, anodised

Accessories

	EMC gasket kit between horizontal rail and horizontal rail	24562-528	Add Item to Project List +
	Countersunk screw, torx (M4x10), steel zinc plated, PU 100 pieces	24560-155	Add Item to Project List +
	Countersunk screw, torx (M4x14), steel zinc plated, PU 100 pieces	24560-130	Add Item to Project List +

EXPLORE	CONTACT	DOWNLOAD
About Us	Customer Service	Download Center
Services & Capabilities	Find a Sales Office or Distributor	Reference Projects
News & Events	Global Locations	Videos
Newsletter Subscriptions	Product Compliance & Certifications	Product Configurators
Strategic Partnerships	Partner Login	Warranties and Terms of Sale & Procurement
Investor Relations		

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

