







Loading-Plan
acc. to TIA/EIA 568B



		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by TAMAS		Inspected by AVRAM		Standardisation HOFFMANN		Date 2016-11-25		State Final Release			
Department EC PD - RO		Title har-port RJ45 coupler Cat.6 AWG 27/7								Doc-Key / ECM-Nr. 100222229/UGD/002/D 500000111080					
HARTING Electronics GmbH D-32339 Espelkamp				Type TB		Number 094545215XX						Rev. D		Page 1/2	

1		2		3		4		5		6		7		8	
A	Line No.	Part number	Type of cable		Length A (m)										A
	1	09 45 452 1500	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,15 (+/-0,03)										
	2	09 45 452 1501	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,20 (+/-0,04)										
	3	09 45 452 1502	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,30 (+/-0,06)										
B	4	09 45 452 1503	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,40 (+/-0,08)										B
	5	09 45 452 1504	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,50 (+/-0,10)										
	6	09 45 452 1505	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,60 (+/-0,12)										
	7	09 45 452 1506	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,70 (+/-0,14)										
	8	09 45 452 1507	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,80 (+/-0,16)										
	9	09 45 452 1508	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		0,90 (+/-0,18)										
	10	09 45 452 1509	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		1,0 (+/-0,20)										
	11	09 45 452 1510	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		1,5 (+/-0,075)										
	12	09 45 452 1511	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		2,0 (+/-0,10)										
	13	09 45 452 1512	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		2,5 (+/-0,125)										
	14	09 45 452 1513	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		3,0 (+/-0,15)										
	15	09 45 452 1514	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		3,5 (+/-0,175)										
C	16	09 45 452 1515	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		4,0 (+/-0,20)										C
	17	09 45 452 1516	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		5,0 (+/-0,25)										
	18	09 45 452 1517	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		7,5 (+/-0,375)										
	19	09 45 452 1518	har-port RJ45 IP20 coupler Cat.6 PFT cable jack silver		10,0 (+/-0,50)										
	20														
	21	09 45 452 1530	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,15 (+/-0,03)										
	22	09 45 452 1531	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,20 (+/-0,04)										
	23	09 45 452 1532	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,30 (+/-0,06)										
D	24	09 45 452 1533	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,40 (+/-0,08)										D
	25	09 45 452 1534	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,50 (+/-0,10)										
	26	09 45 452 1535	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,60 (+/-0,12)										
	27	09 45 452 1536	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,70 (+/-0,14)										
	28	09 45 452 1537	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,80 (+/-0,16)										
	29	09 45 452 1538	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		0,90 (+/-0,18)										
	30	09 45 452 1539	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		1,0 (+/-0,20)										
	31	09 45 452 1540	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		1,5 (+/-0,075)										
	32	09 45 452 1541	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		2,0 (+/-0,10)										
	33	09 45 452 1542	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		2,5 (+/-0,125)										
	34	09 45 452 1543	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		3,0 (+/-0,15)										
	35	09 45 452 1544	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		3,5 (+/-0,175)										
E	36	09 45 452 1545	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		4,0 (+/-0,20)										E
	37	09 45 452 1546	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		5,0 (+/-0,25)										
	38	09 45 452 1547	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		7,5 (+/-0,375)										
	39	09 45 452 1548	har-port RJ45 IP20 coupler Cat.6 PFT cable jack black		10,0 (+/-0,50)										
F															F
1		2		3		4		5		6		7		8	

		All Dimensions in mm Original Size DIN A3		Scale 1:1	Free size tol.		Ref. Sub.		
		All rights reserved Department EC PD - RO		Created by TAMAS	Inspected by AVRAM	Standardisation HOFFMANN	Date 2016-11-25	State Final Release	
HARTING Electronics GmbH D-32339 Espelkamp				Title har-port RJ45 coupler Cat.6 AWG 27/7				Doc-Key / ECM-Nr. 100222229/UGD/002/D 500000111080	
				Type TB	Number 094545215XX			Rev. D	Page 2/2



All rights reserved

Department EC PD - RO

All Dimensions in mm

Original Size DIN A3

Scale 1:1

Free size tol.

Created by

TAMAS

Inspected by

AVRAM

Standardisation

HOFFMANN

Date

2016-11-25

State

Final Release

Title

har-port RJ45 coupler Cat.6 AWG 27/7

Type

TB

Number

094545215XX

Doc-Key / ECM-Nr.

100222229/UGD/002/D

Rev.

D

Page

2/2

HARTING Electronics GmbH

D-32339 Espelkamp

Doc-Key / ECM-Nr.

100222229/UGD/002/D

Rev.

D

Page

2/2

Downloaded from Arrow.com

A3