



**Part Number :** [190670008](#)  
**Product Description :** NylaKrimp Funnel Entry  
Ring Tongue Terminal for 8 AWG Wire, Stud  
Size 1/4" (M6)  
**Series Number :** 19067  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** D-950-14



## Documents & Resources

### Drawings

[190670008\\_sd.pdf](#)

### 3D Models and Design Files

[190670008\\_stp.zip](#)

### Specifications


[PS-19902-011-001.pdf](#)

[PS-19902-013-001.pdf](#)

[PS-19902-016-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6)
Keyword	Ring Terminal, Ring Terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753065314

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	3.348/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/4" (M6)

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	8.98mm max.
Wire Size (AWG)	8

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192890001</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Crimp Tool Kit for 8 AWG Insulated Ring Terminals	<u>640017670</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>

---

This document was generated on Mar 09, 2025