

**Part Number :** [16020085](#)

**Product Description :** SL Crimp Terminal, Series 70058, Female, 36-32 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel

**Series Number :** 70058

**Status :** Active

**Product Category :** Crimp Terminals

**Engineering Part Number :** 70058-0017



---

## Documents and Resources

### Drawings

[016020085 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-70058-001.pdf](#)

[PS-70400-001.pdf](#)

[TS-70058-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	70058
Description	SL Crimp Terminal, Series 70058, Female, 36-32 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel
Application	Wire-to-Board, Wire-to-Wire
Product Name	CyClone,SL
UPC	800753596009

### Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.073/g
Packaging Type	Reel
Plating min - Mating	0.750µm
Plating min - Termination	2.000µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.64mm max.

Wire Size (AWG)	32, 34, 36
Wire Size mm <sup>2</sup>	N/A

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

### Mates With / Use With

#### Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings and CPA Retainers	<u>70066</u>
SL Dual Row Crimp Housings	<u>70450</u>

---

### Application Tooling

#### Global

Description	Part Number
Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals	<u>11020022</u>
PremiumGrade Hand Crimp Tool for SL Crimp Terminals, 24-22 AWG and 36-32 AWG	<u>638118700</u>
FineAdjust Applicator, 36-32 AWG Wire	<u>639003300</u>
T2 Terminator Tooling Die	<u>639103300</u>

---

This document was generated on May 20, 2026