Specification Sheet

Part Number: 111-01196



PA66HIRHSUV material is formulated to withstand extreme climate conditions and vibration.

Inside serrations enhance strong grip on cables and wire bundles.

Head design provides high tensile strength with low insertion force.

Bent tail ensures a quick and simple installation.

Heavy Duty Cable Tie, 22" Long, UL Rated, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Article Number	111-01196
Type	T250M
Color	Black (BK)
Quantity Per	bag
Product Description	These cable ties are manufactured from a specially formulated impact-resistant, heat and UV stabilized PA66 material, delivering increased flexibility while also enduring moisture fluctuations. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 22" Long, UL Rated, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Downloaded from Arrow.com.

Global Part Name	T250M-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	250
Minimum Tensile Strength (Metric)	1115
Length L (Imperial)	22.3
Length L (Metric)	565.3
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.49
Width W (Metric)	12.4
Bundle Diameter Min (Imperial)	0.47
Bundle Diameter Min (Metric)	12.0
Bundle Diameter Max (Imperial)	5.91
Bundle Diameter Max (Metric)	150.0
Thickness T (Imperial)	0.07

Downloaded from Arrow.com.

Thickness T (Metric)	1.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25

Downloaded from Arrow.com.

Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.