Part Number : 988251065
Product Description : NSCC, Pin Connector Hybrid, Unsealed, 6 Circuits, Green
Series Number : 98825
Status : Active
Product Category : Connector Housings
Engineering Part Number : 08315EV6F5



Documents and Resources

Drawings

988251065_sd.pdf

PK-98825-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-98821-001-001.pdf

988210001-AS-CH-001.pdf

510651000-PS-CHI-000.pdf

510651000-PS-JAP-000.pdf

510651000-PS-KOR-000.pdf

510651000-PS-SPA-000.pdf

510651001-PS-CHI-000.pdf

510651001-PS-JAP-000.pdf

510651001-PS-KOR-000.pdf

510651001-PS-SPA-000.pdf

988210001-PS-CH-001.pdf

PS-98821-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant

Downloaded from Arrow.com.

EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	98825
Description	NSCC, Pin Connector Hybrid, Unsealed, 6 Circuits, Green
Application	Wire-to-Wire
Component Type	Plug
Product Name	NSCC
UPC	822348817306

Physical

Circuits Detail	4 x 1.5 + 2 x 2.8
Circuits (maximum)	6
Color - Resin	Green

Downloaded from Arrow.com.

Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	4.700/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.33mm, 4.20mm, 5.00mm
Pitch - Termination Interface	3.33mm, 4.20mm, 5.00mm
Polarized to Mating Part	Yes
Ports	1
Sealed	Unsealed
Stackable	No
Temperature Range - Operating	-40° to +85°C
Terminal Size	1.5, 2.8

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
NSCC, Receptacle Connector Hybrid, Single Part, Unsealed 6 Circuits Green	988211065

Use with Part(s)

Description	Part Number
Use With	Use with FCI Male Terminals

Application Tooling

Downloaded from Arrow.com.

Global

Description	Part Number
Extractor Tool for Unsealed Receptacle Connectors	638133800

Downloaded from Arrow.com.