

**SCHROFF**

Project - 0 item(s)

MY PROJECT LIST

PRODUCTS

APPLICATIONS

INDUSTRIES

NEW PRODUCTS

CONFIGURATORS

Products ▾

Search



Home > Handle, static, trapeziform, plastic, black



Handle, static, trapeziform, plastic, black

SCHROFF**Catalog Number: 20808-085**[Back To Product](#)

- With separate identification plate
- Handles laterally closed
- Identification plate: Al, 1.5 mm
- Anodised, cut edges plain
- Handle: PPE, UL 94 V-1
- Please order clip separately
- Required quantity: 1 handle for 3 U, 2 handles for 6 U

Note:

Cannot be used together with fixing clip (21101-239)

Specification:

IEC 60297-3-101

Handle:

Trapezoid, Static

Type:

Individual Components

Standard:

VME

Individual Component Type:


Handle

Standard pack quantity (SPQ):

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.



Other Views

**Select product specifications before modifying or adding to project list or requesting a quote.**

Width-HP-defining

10

[Clear Selection](#)Quantity [Modify Product](#) ▶[Add Item to Project List](#) +**Documents**

Main Catalog - Plug-in units



User manual

Links

Native CAD files



Technical Data

Width mm	49.4
Qty	1 piece (SPQ 5)
Delivery is exclusively made in Standard Pack Quantity (SPQ)	5
Material	Plastic Lever, UL 94, V-1
Finish	Black
Width HP	10

Delivery Comprises:

Item	Quantity	Description
1a	1	Cantilever plastic handle with 2 alignment pins, PPE, UL 94 V-1, black
2	1	Identification plate, Al, 1.5 mm, anodized, cut edges plain

Accessories

	Square nut, M2.5, St, nickel-plated, PU 100 pieces	21100-359	Add Item to Project List +
	Countersunk screw, cross recess (M2.5x12), steel nickel plated, Pu 100 pcs	21100-507	Add Item to Project List +

EXPLORE	CONTACT	DOWNLOAD
About Us	Customer Service	Download Center
Services & Capabilities	Find a Sales Office or Distributor	Reference Projects
News & Events	Global Locations	Videos
Newsletter Subscriptions	Product Compliance & Certifications	Product Configurators
Strategic Partnerships	Partner Login	Warranties and Terms of Sale & Procurement
Investor Relations		

Connect With Us

