

SLF7055T-4R7N3R1-3PF

**Applications**

Commercial Grade

Wire Wound

Magnetic Shield

Ferrite Core

**Series | Type**

SLF

 EOL announced

Recommended Alternate Part No. : [VLS5045EX-4R7M](#) (Interchangeability is not guaranteed.)

**Status**

Discontinue Issue Date : May.14, 2024

Last Purchase Order Date : Mar.31, 2026

Last Shipment Date : Dec.31, 2026

**Brand**

TDK

**Size**

Length(L)	7.00mm $\pm 0.20$ mm
Width(W)	7.00mm $\pm 0.20$ mm
Thickness   Height	5.50mm $\pm 0.30$ mm
Recommended Land Pattern (A)	1.50mm Nom.
Recommended Land Pattern (B)	4.80mm Nom.
Recommended Land Pattern (C)	2.20mm Nom.

**Electrical Characteristics**

Inductance	4.7 $\mu$ H $\pm 30\%$ at 100kHz
Rated Current (L Change) [Typ.]	
Rated Current (L Change) [Max.]	3.6A (10% Down)
Rated Current (Temperature Rise) [Typ.]	3.1A (30°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	28m $\Omega$
DC Resistance [Max.]	36.4m $\Omega$
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

**Other**

Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
-----------------------	--

! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

## SLF7055T-4R7N3R1-3PF









Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [330mm Reel]
Package Quantity	1000pcs
Weight	0.8g

! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

SLF7055T-4R7N3R1-3PF



## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.


! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

SLF7055T-4R7N3R1-3PF





## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.



## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.