

**Part Number :** [150310609](#)


**Product Description :** 0.30mm Pitch Premo-Flex FFC/FPC Jumper with Notches, Same Side Contacts (Type A), 153.00mm Cable Length, Gold (Au) Plating, 9 Circuits

**Series Number :** 15031

**Status :** Active

**Product Category :** Flat-Flexible Cable (FFC)

---



## Documents and Resources

### Drawings

[150310609\\_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[150310001-000.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | per SJ/T 11365-2006                            |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                 |
| REACH SVHC         | Not Contained per D(2023)8585-DC (23 Jan 2024) |
| EU RoHS            | Compliant per EU 2015/863                      |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

|              |                                                                                                                                                     |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                                              |
| Category     | Flat-Flexible Cable (FFC)                                                                                                                           |
| Series       | 15031                                                                                                                                               |
| Description  | 0.30mm Pitch Premo-Flex FFC/<br>FPC Jumper with Notches, Same<br>Side Contacts (Type A), 153.00mm<br>Cable Length, Gold (Au) Plating, 9<br>Circuits |
| Product Name | Premo-Flex FFC/FPC Jumper                                                                                                                           |
| UPC          | 195842786813                                                                                                                                        |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 0.2A |
| Voltage - Maximum             | N/A  |

**Physical**

|                               |                                        |
|-------------------------------|----------------------------------------|
| Cable Length                  | 152.00mm                               |
| Circuits (Loaded)             | 9                                      |
| Contact Layout Type           | A (same side)                          |
| Design Feature                | Miniaturization, Superior<br>Retention |
| Material - Plating Mating     | Gold                                   |
| Net Weight                    | 0.094/g                                |
| Packaging Type                | Bag                                    |
| Pitch - Mating Interface      | 0.30mm                                 |
| Temperature Range - Operating | -40° to +105°C                         |
| Termination Style             | FFC/FPC Connector                      |

|                 |                                |
|-----------------|--------------------------------|
| Wire/Cable Type | Flexible Printed Circuit (FPC) |
| Wire Size (AWG) | N/A                            |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                                                                                                              | Part Number       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| Easy-On Back Flip FPC Connector with Lock Terminal, 0.30mm Pitch, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 9 Circuits | <u>5047540900</u> |

---

This document was generated on Sep 16, 2026