




1-2273088-4 Product Details

 Share

 Print

 Email



 Active

M8/M12 Connector System

M12 x 1.0 angled plug pigt A

1-2273088-4 

TE Internal Number: 1-2273088-4

Product Highlights [View All](#)

- M12 Series
- Cable Assembly
- Plug
- Male
- Wire Size = 0.33² [22] mm² [AWG]

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type 	Cable Assembly
Connector Type	Plug
Gender	Male
Wire Size (mm² [AWG]) 	0.33² [22]
Thread Size	M12
Mount Angle	Right Angle

Electrical Characteristics

Contact - Rated Current (A)	4 
Operating Voltage (VAC)	125
Operating Voltage (VDC)	125

Dimensions

Cable Length (M [ft]) 	10.00 [32.810]
---	----------------

Body Features

Connector Color	Blue
Insulation Material	PVC
Wire Color	Brown, White, Blue, Black, Gray
Cable Color	Black

Housing Features

Housing Material	Plastic
------------------	---------

Configuration Features

Number of Positions 	5
Shielded	No

Industry Standards

IP Dust Sealing Level	6
IP Water Sealing Level	7
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Identification Marking

Keying	A 
--------	---

Environmental

Operating Temperature (°C [°F])	-25 - +85 [-13 - +185]
---------------------------------	------------------------

Conditions for Usage

Field Serviceable	Yes
-------------------	-----

Operation/Application

Application	Sensors
-------------	---------

Packaging Features

Packaging Quantity	1/Cartron
--------------------	-----------

Other

Series	M12
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

