Part Number : 2002189700
Product Description : Hand Crimp Tool for 1.25mm Pitch PicoBlade Crimp Terminals, 28-26 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

2002189700-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for 1.25mm Pitch PicoBlade Crimp Terminals, 28-26 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PicoBlade
Tool Type	Hand Crimp Tool
UPC	193264527298
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Physical

Net Weight	332.600/g

Applicable Parts

Description	Part Number
1.25mm Pitch, PicoBlade Female Crimp Terminal, 0.38µm Gold (Au) Plating, 28-26 AWG, Reel	500798025
1.25mm Pitch, PicoBlade Female Crimp Terminal, Gold (Au) Flash Plating, 28-26 AWG, Reel	500798020
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-26 AWG, Reel	500798001

Downloaded from Arrow.com.