
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECR–18–013940	04SEP2018	ED	RS



C	B	A	FINISH	PART NUMBER
9.60 [.380]	3.15 [.124]	2.49 [.098]	4	9–413889–4
9.60 [.380]	4.55 [.179]	3.51 [.138]	4	9–413889–3
9.60 [.380]	3.86 [.152]	3.20 [.126]	4	9–413889–2
9.60 [.380]	4.55 [.179]	3.51 [.138]	6	9–413889–1
9.60 [.380]	3.86 [.152]	3.20 [.126]	6	9–413889–0
9.60 [.380]	4.55 [.179]	3.51 [.138]	4	3–413889–4
7.87 [.310]	3.15 [.124]	2.49 [.098]	4	3–413889–3
7.87 [.310]	4.55 [.179]	3.20 [.138]	4	3–413889–2
7.87 [.310]	3.86 [.152]	3.20 [.126]	4	3–413889–1
7.87 [.310]	3.15 [.124]	2.49 [.098]	3	3–413889–0
7.87 [.310]	4.55 [.179]	3.51 [.138]	3	2–413889–7
7.87 [.310]	3.86 [.152]	3.20 [.126]	3	2–413889–4
9.60 [.380]	3.86 [.152]	3.20 [.126]	5	2–413889–1
9.60 [.380]	3.86 [.152]	2.67 [.105]	4	2–413889–0
9.60 [.380]	3.15 [.124]	2.49 [.098]	4	1–413889–9
9.60 [.380]	4.55 [.179]	3.51 [.138]	4	1–413889–8
9.60 [.380]	3.86 [.152]	3.20 [.126]	4	1–413889–7
9.60 [.380]	3.86 [.152]	2.67 [.105]	3	1–413889–6
9.60 [.380]	3.15 [.124]	2.49 [.098]	3	1–413889–5
9.60 [.380]	4.55 [.179]	3.51 [.138]	3	1–413889–4
9.60 [.380]	3.86 [.152]	3.20 [.126]	3	1–413889–3
9.60 [.380]	3.86 [.152]	2.67 [.105]	2	1–413889–2
9.60 [.380]	3.15 [.124]	2.49 [.098]	2	413889–9
9.60 [.380]	4.55 [.179]	3.51 [.138]	2	413889–6
OBSOLETE 9.60 [.380]	3.86 [.152]	3.20 [.126]	2	413889–3

1. COPPER ALLOY
2. BRIGHT TIN–LEAD PLATE PER ASTM B 545 WITH SUPPLEMENTAL ANTI–FRETTING LUBRICANT.
3. NICKEL PLATE.
4. GOLD PLATE
5. BLACK NICKEL PLATE.
6. TIN PLATE PER ASTM B 545 WITH SUPPLEMENTAL ANTI–FRETTING LUBRICANT.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.05 [.002]
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL 1

FINISH SEE TABLE

DWN	M. O'BRINE	29OCT99
CHK	B. MOYER	29OCT99
APVD	B. MOYER	29OCT99
PRODUCT SPEC	–	
APPLICATION SPEC	–	
WEIGHT	0.000000	

TE Connectivity

NAME FERRULE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–413889	–

CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 1 | REV G1

Downloaded from Arrow.com.