Part Number : 1731130002
Product Description : FCT High-Density D-Sub Crimp Housing, Male, 15 Circuits
Series Number : 173113
Status : Active
Product Category : D-Sub Connectors
Engineering Part Number : CT09-15P7



Documents and Resources

Drawings

1731130002_sd.pdf

Specifications

1731120006-PK-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173113
Description	FCT High-Density D-Sub Crimp Housing, Male, 15 Circuits
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	High Density
UPC	889056254977

Electrical

Shielded	Yes

Physical

Circuits (Loaded)	0
Circuits (maximum)	15
Color - Resin	Black
Gender	Male
Material - Resin	Polybutylene Terephthalate (PBT)
Material - Shell	Steel
Net Weight	4.000/g
Number of Rows	3
Orientation	Straight
Packaging Type	Tray
Panel Mount	Rear
Panel Mount Method	Flange
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	1.98mm

Downloaded from Arrow.com.

Pitch - Termination Interface	1.98mm
Plating - Shell	Nickel
Polarized to Mating Part	Yes
Ports	1
Shell Size	1
Temperature Range - Operating	-55° to +105°C
Termination Style	Crimp
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20
Wire Size (AWG)	22, 24, 26, 28

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT High-Density D-Sub, Size 1, 15 Position, Socket

Use with Part(s)

Description	Part Number
FCT Machined Contact, Male, Crimp, 0.20µm Gold Plating, 28-22 AWG, 500 Pieces	1731120223
FCT Machined Contact, Male, Crimp, 0.80µm Gold Plating, 28-22 AWG, 500 Pieces	1731120224
FCT Machined Contact, Male, Crimp, 1.30µm Gold Plating, 28-22 AWG, 500 Pieces	1731120225

Downloaded from Arrow.com.