






Color: ■ gray

Similar to illustration



DIN-rail-mount PCB carrier, size 1



Dimensions in mm
L1 = PCB length
L2 = L1 - 11 mm (L2 = carrier base length)
L3 = L1 + 2 mm

DIN-rail mount PCB carrier, size 1 – carrier base, size 1; 1 m long

Note	
Note	Length calculation for a complete mounting carrier: · PCB length: L1 · Base length: L2 = L1 - 11 mm · Mounting carrier length: L3 = L1 + 2 mm · Lateral cover, size 1, 6.35 mm thick · Free space between base and PCB (when using upper PCB groove): 5 mm PCB tolerances: 1.5 mm ± 0.2 mm (thickness), ± 0.2 mm (length/width), -0.1/+0.3 for milling contours



Physical data	
Width	1000 mm / 39.37 inches
Height	71.2 mm / 2.803 inches

Mechanical data	
Mounting type	DIN-35 rail

Material data	
Color	gray
Housing material	PC/ABS

Commercial data	
Product Group	6 (INTERFACE ELECTRONIC)
PU (SPU)	1 (1) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332639484
Customs tariff number	39169010900

Product Classification		
UNSPSC		39121321
eCl@ss 10.0		27-18-27-02
eCl@ss 9.0		27-18-27-02
ETIM 9.0		EC001031
ETIM 8.0		EC001031
ECCN		NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 288-600	

CAD/CAE-Data

CAD data	
2D/3D Models 288-600	

CAE data	
WSCAD Universe 288-600	
ZUKEN Portal 288-600	



1 Compatible Products

1.1 Optional Accessories

1.1.1 Installation

1.1.1.1 Mounting accessories



[Item No.: 210-533](#)
Phillips screw 2.9 x 13

1.1.1.2 Mounting carrier and mounting feet



[Item No.: 288-602](#)
Fixing foot for DIN 35 rail; gray



[Item No.: 288-601](#)
Lateral cover; Size 1; small; 6.35 mm thick; gray

1.1.2 Marking

1.1.2.1 Marking strip



[Item No.: 709-196](#)
Marking strips; for laser printer; translucent



[Item No.: 709-177](#)
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; translucent



[Item No.: 709-178](#)
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; white