

Straight Blade Devices
2 Pole, 3 Wire Grounding
15 and 20 Ampere, 125 Volts
INSULGRIP® Connector Bodies



HBL5269C



HBL8219C



Insulgrip Connector Bodies

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.230"-.720" (5.8-18.3)	HBL5269C™	HBL5369C™
Corrosion resistant yellow nylon.	.230"-.720" (5.8-18.3)	HBL52CM69C	HBL53CM69C

Insulgrip Hospital Grade Connector Bodies

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.230"-.720" (5.8-18.3)	HBL8219C™	HBL8319C
Transparent housing.	.230"-.720" (5.8-18.3)	HBL8219CT	HBL8319CT

Accessories

Seat-Tite® triple seal black elastomer cover for Insulgrip® connector bodies when used in a cord set.	HBL6018*
Same as above except yellow.	HBL60CM18*
Closure plug, black.	HBL6019
Closure plug, yellow.	HBL60CM19
PLUGOUT® lockout device for Hubbell plugs and others.	HLD

Notes: *IP55 suitability if closure plug inserted or when installed and used properly with HBL6017 or HBL60CM17.

Straight Blade Devices

2 Pole, 3 Wire Grounding

15 and 20 Ampere, 250 Volts

Connector Bodies and Flanged Receptacles
IP20
SUITABILITY

 NEMA 6-15R
15A 250V
UL CSA

 NEMA 6-20R
20A 250V
UL Listed
Connector Bodies





Description	Cord Dia.	Catalog Numbers	
Insulgrip® connector body, black and white nylon, multiple drive screws.	.230"-.720" (5.8-18.3)	HBL5669C	HBL5469C
ERGO™ Grip connector body, overmolded yellow nylon.	.220"-.600" (5.6-15.25)	HBL5567EY	HBL5579EY
Valise® connector body, yellow nylon.	.220"-.660" (5.6-16.8)	HBL5669VY	HBL5469VY

ERGO™ Grip Hospital Grade Connector Bodies

Description	Cord Dia.	Catalog Numbers	
Overmolded white nylon.	.300"-.600" (7.6-15.25)	HBL8567E	HBL8579E

Valise® Hospital Grade Connector Body

Description	Cord Dia.	Catalog Number	
White nylon.	.300"-.660" (7.6-16.8)	—	HBL8469V

**HBL5669C****HBL5567EY****HBL5669VY****HBL5679C****HBL5656**
 NEMA 6-15R
15A 250V
UL CSA

 NEMA 6-20R
20A 250V
UL Listed
Flanged Receptacles

Description	Catalog Numbers	
Nylon casing, multiple drive screws.	HBL5679C	HBL5479C
Stainless steel flange, brown phenolic housing (mounting screws packaged separately).	HBL5656	—