

NOTES:

1. MATERIALS AND FINISHES:

HD-BNC STR CRIMP PLUG - 34-1026
1.0/2.3 PULL-PUSH CRIMP PLUG - 282138-75
CABLE - BELDEN 1855A

2. ELECTRICAL:

A. IMPEDANCE: 75 OHM



3. PACKAGING:

A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-850-155XXXX AND DATE CODE".

THIRD ANGLE PROJ. 

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	5/15/15	50350	NR/BCG
B	HST REMOVED	6/30/15	50581	NR/BCG



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH "L" IN INCHES [METERS]
95-850-155-006	-	6.00 [0.152]
	95-850-155M025	9.84 [0.250]
95-850-155-012	-	12.00 [0.305]
95-850-155-018	-	18.00 [0.457]
-	95-850-155M050	19.69 [0.500]
95-850-155-024	-	24.00 [0.610]
-	95-850-155M075	29.53 [0.750]
95-850-155-036	-	36.00 [0.914]
-	95-850-155M100	39.37 [1.000]
95-850-155-048	-	48.00 [1.219]
-	95-850-155M200	78.74 [2.000]
	95-850-155M400	157.48 [4.000]

DESIGN REQUIREMENTS:

 FREQUENCY : DC TO 4 GHz CONTINUITY VSWR : ----- MAX HI-POT: 500 VRMS INS. LOSS ----- dB MAX OTHER

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES
±.015 (0.381 mm) ±.005 (0.127 mm) ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL
SEE NOTES

DRAWN
RAJAGOPAL N
DATE
09-Dec-14

TITLE
HD-BNC STR CRIMP PLUG TO
1.0/2.3 PUSH-PULL CRIMP PLUG,
USING BELDEN 1855A CABLE,
VARIOUS LENGTHS

SCALE: 2.5:1.0

SHEET 2 OF 2

DWG SIZE B

REV B

REFERENCE
EAR # 6515
CONFIGURATION LEVEL: In Work
FINISH

APPROVED
K. CAPOZZI
DATE
6/30/15

ITEM NO. 95-850-155XXXX

PART NO. 95-850-155XXXX

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

Amphenol RF

www.amphenolrf.com

DRAWING NO. 95-850-155XXXX

ITEM NO. 95-850-155XXXX

PART NO. 95-850-155XXXX