



## GD2026, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GD2026](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or  
Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 3" to 3-1/2" Rod, 3" Pipe



## Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

## Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

## Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Industry Standard(s)	No
Buy America(n) Qualified Certification - ETL	UL467
Standards - Industry Standards Met	Contact Manufacturer
Standards - RoHS Compliance Status	No
Certification - CSA Approved	Yes
UL Listed	Yes
Certification - UL Listed Direct Burial	Yes

## Conductor

Conductor - Rod Size	3 in
Conductor - Copper Str Size	<ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li></ul>
Conductor - Rod Size Range	3 in
Conductor - Copper Solid Size	<ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li></ul>
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size B Range	3

Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3

## Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.63 in
Package Height	0.000 in
Dimension - Height mm	143 mm
Dimension - Width fraction	4-7/8 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm
Dimension - B Length inch	1.50 in

## Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

## General

Material Type - Screw	DURIUM™ Silicon Bronze
Sub Brand	MECHANICAL CONNECTOR
Plated	N
Type	GD
U Bolt Type	258
UPC 12 Digit	781810260388
UPC 14 Digit GTIN	00781810260388
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC	781810260388

## Logistics

Minimum Pack Quantity	1
Carton Quantity	6
Pallet Quantity	900

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
BRDY-GD2026-SPEC-EN | REV 4/2026