**Part Number :** 1301370232
**Product Description :** Watertite GFCI Multiple Outlet FD Box with Ground Continuity Monitor, (1) L5-15 Duplex with Flip Lids, 1.83m (6.0') Cord Length, 14/3 SOOW Cord, NEMA L5-15 Watertite Plug
**Series Number :** 130137
**Status :** Not Recommended For New Design
**Product Category :** Power Distribution
**Engineering Part Number :** 3302GGFL143




## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Relevant |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

## Part Details

### General

| | |
|---|---|
| Status | Not Recommended For New Design |
| Category | Power Distribution |
| Series | 130137 |
| Description | Watertite GFCI Multiple Outlet FD Box with Ground Continuity Monitor, (1) L5-15 Duplex with Flip Lids, 1.83m (6.0') Cord Length, 14/3 SOOW Cord, NEMA L5-15 Watertite Plug |
| Enclosure Rating | NEMA 4X |
| NEMA Configuration | NEMA L5-15 |
| Product Name | Watertite |
| Type | GFCI Multiple Outlet Box |
| UPC | 78678898116 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 15.0A |
| GFCI | Yes |
| GFCI Reset | Manual |
| Ground Continuity Monitor | Yes |
| Open Neutral Relay | No |
| Voltage - Maximum | 120V |

### Physical

| | |
|---|---|
| Cord Diameter | 13.59mm (.535") |
| Cord Grip Body Size | F3 3/4" |
| Cord Length | 1.83m (6.0') |
| Cord Type | 14/3 SOOW |
| Feed-Thru | No |
| Flip Lid | Yes |
| Material - Housing | Nylon |
| Mounting Style | Portable |
| Number of Receptacles | 1 |

Downloaded from Arrow.com.

| | |
|---|---|
| Packaging Type | Carton |
| Receptacle Type | Duplex |



Downloaded from Arrow.com.