

Product data sheet

Specifications



APC 17" Rack LCD Console - German

AP5717G

-  **Discontinued on:** Jul 31, 2024
-  **To be end-of-service on:** Jul 31, 2027

 **Discontinued - Service only**

Overview

Lead time Usually in Stock

Main

Main Input Voltage	100 V 240 V
Number of rack unit	1U
Provided equipment	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Single user rack mount kit USB cable USB KVM cable

Physical

Colour	Black
Height	44 mm
Width	482 mm
Depth	614 mm
Net weight	15.9 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted
Maximum mounting depth	1049.8 mm
Minimum mounting depth	680 mm

Input

Network frequency 50/60 Hz

Conformance

Product certifications	C-Tick GOST Industry Canada NOM UL listed VDE
------------------------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 55022 class A EN 55024 EN 60950 FCC part 15 class A IEC 60950
-----------	--

Environmental

Ambient air temperature for operation	0...40 °C
---------------------------------------	-----------

Supported Hardware

Display colour	16 colours
Display size	17 inch
Trackball type	PS/2 touchpad USB mouse
Display type	LCD display
Display power consumption	19 W
Pixel size	0.26

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	82.6 cm
Package 1 Length	67.3 cm
Package 1 Weight	19.46 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACH Regulation	REACH Declaration
Halogen-free status	Product contains halogen above thresholds

Use Again

 Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative



