


CLIFF

BLACK METAL FEEDTHROUGH CONNECTORS FT Series

The Black Metal FT Series of true feed through connectors are perfect for developing custom I/O configurations for wall-plates, rack panels, etc. ALL fit within a standard XLR panel cutout, and use common cabling for front and back connections. No soldering, no punch terminations, just use the standard cable for that particular connector style. Mount from the front or back, low rear profile accommodates the tightest “behind the panel” spaces. Available in a wide variety of styles. The frame is made from diecast metal and has a matt black finish.



Part No.
CP30200GMB
CP30200GM3B

Description
 HDMI A Female to HDMI A, Gold Plated, CSK hole.
 HDMI A Female to HDMI A, Gold Plated, M3 hole.



Part No.
CP30202MB
CP30202M3B

Description
 Mini Displayport, CSK hole.
 Mini Displayport, M3 hole.



Part No.
CP30203NMB
CP30203NM3B

Description
 USB 2.0 B to USB 2.0 B, CSK hole.
 USB 2.0 B to USB 2.0 B, M3 hole.



Part No.
CP30204NMB
CP30204NM3B

Description
 USB 3.0 B to USB 3.0 B, CSK hole.
 USB 3.0 B to USB 3.0 B, M3 hole.



Part No.
CP30205NMB USB 3.0 A to USB 3.0 A, CSK hole.
CP30205NM3B USB 3.0 A to USB 3.0 A, M3 hole.



Part No.
CP30206NMB USB 3.0 B to USB 3.0 A, CSK hole.
CP30206NM3B USB 3.0 B to USB 3.0 A, M3 hole.



Part No.
CP30207NMB USB 2.0 B to USB 2.0 A, CSK hole.
CP30207NM3B USB 2.0 B to USB 2.0 A, M3 hole.



Part No.
CP30208NMB USB 2.0 A to USB 2.0 A, CSK hole.
CP30208NM3B USB 2.0 A to USB 2.0 A, M3 hole.



Part No.
CP30209NMB USB 2.0 A to USB 2.0 B, CSK hole.
CP30209NM3B USB 2.0 A to USB 2.0 B, M3 hole.




Part No.
CP30209NMB USB 2.0 A to USB 2.0 B, CSK hole.
CP30209NM3B USB 2.0 A to USB 2.0 B, M3 hole.



Part No.
CP30211MB USB C Female to Male, CSK hole.
CP30211M3B USB C Female to Male, M3 hole.




Part No.
CP30212MB Dual USB C Female to Male, CSK hole.
CP30212M3B Dual USB C Female to Male, M3 hole.



Part No.
CP30213MB
CP30213M3B

Description
LC Duplex SM adaptor, CSK Hole
LC Duplex SM adaptor, M3 Hole



Part No.
CP30214MB
CP30214M3B

Description
LC Duplex MM, CSK Hole
LC Duplex MM, M3 Hole



Part No.
CP30215MB
CP30215M3B

Description
SC Simplex SM, CSK Hole
SC Simplex SM, M3 Hole



Part No.
CP30216MB
CP30216M3B

Description
SC Simplex MM, CSK Hole
SC Simplex MM, M3 Hole



Part No.
CP30217MB
CP30217M3B

Description
Toslink, CSK Hole
Toslink, M3 Hole



Part No.
CP30218MB
CP30218M3B

Description
ST Fibre, CSK Hole
ST Fibre, M3 Hole



Part No.
CP30219MB
CP30219M3B


Description
FC Fibre, CSK Hole
FC Fibre, M3 Hole

NEW



Part No.
CP30220MB
CP30220M3B

Description
UTP Cat5e RJ45-RJ45, CSK Hole
UTP Cat5e RJ45-RJ45, M3 Hole




Part No.
CP30220SMB
CP30220SM3B

Description
FTP Cat5e RJ45-RJ45, Shielded, CSK Hole
FTP Cat5e RJ45-RJ45, Shielded, M3 Hole




Part No.
CP30222MB
CP30222M3B

Description
UTP Cat6 RJ45-RJ45, CSK Hole
UTP Cat6 RJ45-RJ45, M3 Hole



Part No.
CP30222SMB
CP30222SM3B

Description
FTP Cat6 RJ45-RJ45, Shielded, CSK Hole
FTP Cat6 RJ45-RJ45, Shielded, M3 Hole



Part No.
CP30225SMB
CP30225SM3B

Description
FTP Cat6A RJ45-RJ45, Shielded, CSK Hole
FTP Cat6A RJ45-RJ45, Shielded, M3 Hole



Part No.
CP30229BM

Description
15 Pin VGA Female to Female, CSK Hole

NEW



Part No.
CP30230MB
CP30230M3B

Description
RCA Phono RED, CSK Hole
RCA Phono RED, M3 Hole



Part No.
CP30231MB
CP30231M3B

Description
RCA Phono WHITE, CSK Hole
RCA Phono WHITE, M3 Hole



Part No.
CP30232MB
CP30232M3B

Description
RCA Phono YELLOW, CSK Hole
RCA Phono YELLOW, M3 Hole

Other colours available on request.



Part No.
CP30241MB
CP30241M3B

Description
 Blanking Plate, CSK Hole
 Blanking Plate, M3 Hole



Part No.
CP30114

Description
 XLR USB A to USB B, CSK Hole



Part No.
CP30115

Description
 XLR USB B to USB A, CSK Hole



CP30112 - Sealing Cover for CP30114,
 CP30115 and CP30122 only.



Part No.
CP30120

Description
 XLR 50 OHM BNC, CSK Hole



Part No.
CP30121

Description
 XLR 75 OHM BNC, CSK Hole



Part No.
CP30122

Description
 XLR HDMI A-A, CSK Hole



Part No.
CP30125

Description
 XLR 50 OHM INSULATED BNC, CSK Hole



Part No.
CP30126

Description
 XLR 75 OHM INSULATED BNC, CSK Hole



Part No.
CP303112GMB


Description
12GHz Gold BNC 75 Ohm, CSK Hole

For further information, contact sales@cliffuk.co.uk

Cliff Electronic Components Limited

76 Holmethorpe Avenue, Holmethorpe Ind. Estate,
Redhill, Surrey RH1 2PF U.K.

Tel: +44 (0)1737 771375 Fax: +44 (0)1737 766012



www.cliffuk.co.uk